

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858348

Luminaire Tested: **LD4C10W2N2765D010 4LBWH_6500K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858348
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10W2N2765D010 4LBWH_6500K
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 6500K, W2N2765 LEDS AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 942.0 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858348

CATALOG NUMBER: LD4C10W2N2765D010 4LBWH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P858348

CATALOG NUMBER: LD4C10W2N2765D010 4LBWH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74597
5°	74882
10°	75111
15°	75104
20°	74691
25°	72942
30°	68177
35°	59046
40°	46124
45°	33098
50°	21502
55°	12873
60°	7519
65°	4826
70°	3233
75°	2421
80°	1839
85°	0



TEST NUMBER: P858348

CATALOG NUMBER: LD4C10W2N2765D010 4LBWH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.8	6.1
10°-20°	166.6	17.7
20°-30°	245.8	26.1
30°-40°	242.6	25.8
40°-50°	148.5	15.8
50°-60°	56.9	6.0
60°-70°	17.8	1.9
70°-80°	5.2	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	470.3	49.9
0°-40°	712.9	75.7
0°-60°	918.3	97.5
0°-90°	942.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	942.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	607	
5°	607	58
15°	590	167
25°	538	246
35°	394	243
45°	190	148
55°	60	57
65°	17	18
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P858348

CATALOG NUMBER: LD4C10W2N2765D010 4LBWH_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	607.2
2.5°	608.5
5°	607.2
7.5°	605.9
10°	602.1
12.5°	596.9
15°	590.5
17.5°	582.9
20°	571.3
22.5°	558.6
25°	538.1
27.5°	512.6
30°	480.6
32.5°	441.0
35°	393.7
37.5°	341.3
40°	287.6
42.5°	237.8
45°	190.5
47.5°	148.2
50°	112.5
52.5°	83.1
55°	60.1
57.5°	42.2
60°	30.6
62.5°	23.0
65°	16.6
67.5°	12.8
70°	9.0
72.5°	6.4
75°	5.1
77.5°	2.6
80°	2.6
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)