

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858352

Luminaire Tested: **LD4C10W2N2765D010 4LBWLI\_4000K**

Issue Date: 11/9/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P858352  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 11/9/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C10W2N2765D010 4LBWLI\_4000K  
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, W2N2765 LEDS  
AND 4LBWLI TRIM WITH FINISH  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1041.0 lumens  
Efficiency: N/A  
Efficacy: 80.1 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 13  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858352

CATALOG NUMBER: LD4C10W2N2765D010 4LBWLI\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P858352

CATALOG NUMBER: LD4C10W2N2765D010 4LBWLI\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	78356
5°	79691
10°	83295
15°	88408
20°	92275
25°	91472
30°	85073
35°	72769
40°	55441
45°	32524
50°	13895
55°	4091
60°	1179
65°	698
70°	431
75°	570
80°	0
85°	0



TEST NUMBER: P858352

CATALOG NUMBER: LD4C10W2N2765D010 4LBWLI\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.4	6.0
10°-20°	196.8	18.9
20°-30°	307.1	29.5
30°-40°	298.8	28.7
40°-50°	149.2	14.3
50°-60°	23.1	2.2
60°-70°	2.8	0.3
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	566.3	54.4
0°-40°	865.1	83.1
0°-60°	1037.4	99.7
0°-90°	1041.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1041.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	638	
5°	646	62
15°	695	197
25°	675	307
35°	485	299
45°	187	149
55°	19	23
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P858352

CATALOG NUMBER: LD4C10W2N2765D010 4LBWLI\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	637.8
2.5°	640.2
5°	646.2
7.5°	655.7
10°	667.7
12.5°	683.1
15°	695.1
17.5°	704.6
20°	705.8
22.5°	697.4
25°	674.8
27.5°	641.4
30°	599.7
32.5°	547.3
35°	485.2
37.5°	417.3
40°	345.7
42.5°	269.5
45°	187.2
47.5°	120.4
50°	72.7
52.5°	39.3
55°	19.1
57.5°	8.4
60°	4.8
62.5°	3.6
65°	2.4
67.5°	2.4
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)