

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857460

Luminaire Tested: **LX4C25D010 EX4C259830 4LBSLI**

Issue Date: 2/9/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857460  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/9/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C25D010 EX4C259830 4LBSLI  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2285.5 lumens  
Efficiency: N/A  
Efficacy: 72.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857460

CATALOG NUMBER: LX4C25D010 EX4C259830 4LBSLI

### Luminous Intensity Polar Plot





TEST NUMBER: P857460

CATALOG NUMBER: LX4C25D010 EX4C259830 4LBSLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			71
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			57
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	200497
5°	195948
10°	184004
15°	171194
20°	158781
25°	144744
30°	128851
35°	114207
40°	102655
45°	91874
50°	78820
55°	63421
60°	47249
65°	30174
70°	14548
75°	2421
80°	1769
85°	0



TEST NUMBER: P857460

CATALOG NUMBER: LX4C25D010 EX4C259830 4LBSLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.0	6.5
10°-20°	377.4	16.5
20°-30°	489.0	21.4
30°-40°	479.1	21.0
40°-50°	406.1	17.8
50°-60°	266.3	11.6
60°-70°	107.0	4.7
70°-80°	12.2	0.5
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1014.4	44.4
0°-40°	1493.6	65.3
0°-60°	2165.9	94.8
0°-90°	2285.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2285.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1632	
5°	1589	148
15°	1346	377
25°	1068	489
35°	762	479
45°	529	406
55°	296	266
65°	104	107
75°	5	12
85°	0	0
90°	0	



TEST NUMBER: P857460

CATALOG NUMBER: LX4C25D010 EX4C259830 4LBSLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1632.0
2.5°	1619.3
5°	1588.9
7.5°	1538.3
10°	1475.0
12.5°	1406.7
15°	1346.0
17.5°	1280.3
20°	1214.5
22.5°	1143.7
25°	1067.8
27.5°	989.3
30°	908.3
32.5°	832.4
35°	761.5
37.5°	703.4
40°	640.1
42.5°	584.4
45°	528.8
47.5°	470.6
50°	412.4
52.5°	354.2
55°	296.1
57.5°	242.9
60°	192.3
62.5°	146.7
65°	103.8
67.5°	68.3
70°	40.5
72.5°	17.7
75°	5.1
77.5°	2.5
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)