

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857468

Luminaire Tested: **LX4C25D010 EX4C259835 4LBMH**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857468  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C25D010 EX4C259835 4LBMH  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1701.5 lumens  
Efficiency: N/A  
Efficacy: 54.0 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857468

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBMH

### Luminous Intensity Polar Plot





TEST NUMBER: P857468

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	134733
5°	135248
10°	135664
15°	135658
20°	134922
25°	131758
30°	123148
35°	106648
40°	83298
45°	59767
50°	38818
55°	23239
60°	13612
65°	8750
70°	5783
75°	4414
80°	3254
85°	0



TEST NUMBER: P857468

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.4	6.1
10°-20°	300.9	17.7
20°-30°	444.1	26.1
30°-40°	438.2	25.8
40°-50°	268.2	15.8
50°-60°	102.8	6.0
60°-70°	32.2	1.9
70°-80°	9.4	0.6
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	849.4	49.9
0°-40°	1287.7	75.7
0°-60°	1658.6	97.5
0°-90°	1701.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1701.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1097	
5°	1097	104
15°	1067	301
25°	972	444
35°	711	438
45°	344	268
55°	108	103
65°	30	32
75°	9	9
85°	0	1
90°	0	



TEST NUMBER: P857468

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1096.7
2.5°	1099.0
5°	1096.7
7.5°	1094.3
10°	1087.5
12.5°	1078.2
15°	1066.6
17.5°	1052.8
20°	1032.0
22.5°	1009.0
25°	972.0
27.5°	925.8
30°	868.1
32.5°	796.6
35°	711.1
37.5°	616.4
40°	519.4
42.5°	429.5
45°	344.0
47.5°	267.8
50°	203.1
52.5°	150.1
55°	108.5
57.5°	76.2
60°	55.4
62.5°	41.6
65°	30.1
67.5°	23.1
70°	16.1
72.5°	11.6
75°	9.3
77.5°	4.6
80°	4.6
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)