

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857469

Luminaire Tested: **LX4C25D010 EX4C259835 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P857469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C25D010 EX4C259835 4LBMLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2123.2 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857469

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P857469

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	671271
5°	604072
10°	468294
15°	338954
20°	234701
25°	171096
30°	124311
35°	73563
40°	30936
45°	9660
50°	1242
55°	707
60°	811
65°	959
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P857469

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	430.6	20.3
10°-20°	737.2	34.7
20°-30°	585.9	27.6
30°-40°	310.1	14.6
40°-50°	53.4	2.5
50°-60°	4.0	0.2
60°-70°	2.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1753.7	82.6
0°-40°	2063.8	97.2
0°-60°	2121.2	99.9
0°-90°	2123.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2123.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5464	
5°	4898	431
15°	2665	737
25°	1262	586
35°	490	310
45°	56	53
55°	3	4
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P857469

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5464.0
2.5°	5323.3
5°	4898.3
7.5°	4342.4
10°	3753.9
12.5°	3184.9
15°	2665.0
17.5°	2181.0
20°	1795.2
22.5°	1500.8
25°	1262.2
27.5°	1069.3
30°	876.3
32.5°	680.1
35°	490.5
37.5°	323.8
40°	192.9
42.5°	111.2
45°	55.6
47.5°	19.6
50°	6.5
52.5°	6.5
55°	3.3
57.5°	3.3
60°	3.3
62.5°	3.3
65°	3.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)