

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858386

Luminaire Tested: **LD4C15W2N2050D010 4LBWH_2700K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15W2N2050D010 4LBWH_2700K
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, W2N2050 LEDS AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1083.0 lumens
Efficiency: N/A
Efficacy: 56.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 19.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858386

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P858386

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85764
5°	86092
10°	86351
15°	86347
20°	85882
25°	83867
30°	78391
35°	67879
40°	53020
45°	38049
50°	24713
55°	14800
60°	8649
65°	5552
70°	3700
75°	2801
80°	2052
85°	0



TEST NUMBER: P858386

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	6.1
10°-20°	191.5	17.7
20°-30°	282.7	26.1
30°-40°	278.9	25.8
40°-50°	170.7	15.8
50°-60°	65.4	6.0
60°-70°	20.5	1.9
70°-80°	6.0	0.6
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	540.7	49.9
0°-40°	819.6	75.7
0°-60°	1055.7	97.5
0°-90°	1083.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1083.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	698	
5°	698	66
15°	679	192
25°	619	283
35°	453	279
45°	219	171
55°	69	65
65°	19	20
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P858386

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	698.1
2.5°	699.5
5°	698.1
7.5°	696.6
10°	692.2
12.5°	686.3
15°	678.9
17.5°	670.1
20°	656.9
22.5°	642.2
25°	618.7
27.5°	589.3
30°	552.6
32.5°	507.0
35°	452.6
37.5°	392.4
40°	330.6
42.5°	273.3
45°	219.0
47.5°	170.4
50°	129.3
52.5°	95.5
55°	69.1
57.5°	48.5
60°	35.2
62.5°	26.5
65°	19.1
67.5°	14.7
70°	10.3
72.5°	7.4
75°	5.9
77.5°	2.9
80°	2.9
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)