

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857471

Luminaire Tested: **LX4C25D010 EX4C259835 4LBNLI**

Issue Date: 1/21/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P857471  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C25D010 EX4C259835 4LBNLI  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1665.8 lumens  
Efficiency: N/A  
Efficacy: 52.9 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P857471

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P857471

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	526648
5°	473929
10°	367397
15°	265923
20°	184118
25°	134239
30°	97528
35°	57711
40°	24265
45°	7575
50°	994
55°	557
60°	639
65°	756
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P857471

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	337.8	20.3
10°-20°	578.4	34.7
20°-30°	459.7	27.6
30°-40°	243.3	14.6
40°-50°	41.9	2.5
50°-60°	3.2	0.2
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1375.8	82.6
0°-40°	1619.2	97.2
0°-60°	1664.2	99.9
0°-90°	1665.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1665.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4287	
5°	3843	338
15°	2091	578
25°	990	460
35°	385	243
45°	44	42
55°	3	3
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P857471

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBNLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4286.8
2.5°	4176.4
5°	3843.0
7.5°	3406.9
10°	2945.1
12.5°	2498.7
15°	2090.8
17.5°	1711.1
20°	1408.3
22.5°	1177.5
25°	990.3
27.5°	838.9
30°	687.5
32.5°	533.6
35°	384.8
37.5°	254.1
40°	151.3
42.5°	87.2
45°	43.6
47.5°	15.4
50°	5.2
52.5°	5.2
55°	2.6
57.5°	2.6
60°	2.6
62.5°	2.6
65°	2.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)