

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858387

Luminaire Tested: **LD4C15W2N2050D010 4LBWH_3000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15W2N2050D010 4LBWH_3000K
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, W2N2050 LEDS AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1263.0 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 19.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858387

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P858387

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100015
5°	100397
10°	100697
15°	100707
20°	100145
25°	97802
30°	91414
35°	79158
40°	61840
45°	44373
50°	28822
55°	17264
60°	10099
65°	6483
70°	4310
75°	3275
80°	2405
85°	0



TEST NUMBER: P858387

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.5	6.1
10°-20°	223.4	17.7
20°-30°	329.6	26.1
30°-40°	325.3	25.8
40°-50°	199.1	15.8
50°-60°	76.3	6.0
60°-70°	23.9	1.9
70°-80°	7.0	0.6
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	630.5	49.9
0°-40°	955.8	75.7
0°-60°	1231.2	97.5
0°-90°	1263.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1263.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	814	
5°	814	78
15°	792	223
25°	722	330
35°	528	325
45°	255	199
55°	81	76
65°	22	24
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P858387

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	814.1
2.5°	815.8
5°	814.1
7.5°	812.4
10°	807.2
12.5°	800.4
15°	791.8
17.5°	781.5
20°	766.0
22.5°	749.0
25°	721.5
27.5°	687.2
30°	644.4
32.5°	591.3
35°	527.8
37.5°	457.6
40°	385.6
42.5°	318.8
45°	255.4
47.5°	198.8
50°	150.8
52.5°	111.4
55°	80.6
57.5°	56.5
60°	41.1
62.5°	30.9
65°	22.3
67.5°	17.2
70°	12.0
72.5°	8.6
75°	6.9
77.5°	3.4
80°	3.4
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)