

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857475

Luminaire Tested: **LX4C25D010 EX4C259835 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P857475
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C25D010 EX4C259835 4LBWH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1891.4 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857475

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P857475

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82																			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67																			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61																			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55																			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50																			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																			
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43																			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149771
5°	150343
10°	150796
15°	150806
20°	149969
25°	146466
30°	136894
35°	118541
40°	92600
45°	66456
50°	43175
55°	25853
60°	15111
65°	9709
70°	6466
75°	4889
80°	3679
85°	0



TEST NUMBER: P857475

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.1	6.1
10°-20°	334.5	17.7
20°-30°	493.6	26.1
30°-40°	487.1	25.8
40°-50°	298.1	15.8
50°-60°	114.3	6.0
60°-70°	35.7	1.9
70°-80°	10.5	0.6
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	944.3	49.9
0°-40°	1431.4	75.7
0°-60°	1843.8	97.5
0°-90°	1891.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1891.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1219	
5°	1219	116
15°	1186	335
25°	1080	494
35°	790	487
45°	382	298
55°	121	114
65°	33	36
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P857475

CATALOG NUMBER: LX4C25D010 EX4C259835 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1219.1
2.5°	1221.7
5°	1219.1
7.5°	1216.5
10°	1208.8
12.5°	1198.6
15°	1185.7
17.5°	1170.3
20°	1147.1
22.5°	1121.6
25°	1080.5
27.5°	1029.2
30°	965.0
32.5°	885.5
35°	790.4
37.5°	685.2
40°	577.4
42.5°	477.3
45°	382.5
47.5°	297.7
50°	225.9
52.5°	166.8
55°	120.7
57.5°	84.6
60°	61.5
62.5°	46.3
65°	33.4
67.5°	25.7
70°	18.0
72.5°	12.8
75°	10.3
77.5°	5.2
80°	5.2
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)