

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858437

Luminaire Tested: **LD4C15W2N2765D010 4LBWLI\_5000K**

Issue Date: 11/9/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P858437  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 11/9/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C15W2N2765D010 4LBWLI\_5000K  
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2765 LEDS  
AND 4LBWLI TRIM WITH FINISH  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1480.0 lumens  
Efficiency: N/A  
Efficacy: 77.1 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858437

CATALOG NUMBER: LD4C15W2N2765D010 4LBWLI\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P858437

CATALOG NUMBER: LD4C15W2N2765D010 4LBWLI\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	111404
5°	113297
10°	118411
15°	125686
20°	131182
25°	130050
30°	120949
35°	103469
40°	78824
45°	46232
50°	19762
55°	5826
60°	1671
65°	988
70°	611
75°	807
80°	0
85°	0



TEST NUMBER: P858437

CATALOG NUMBER: LD4C15W2N2765D010 4LBWLI\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.7	6.0
10°-20°	279.9	18.9
20°-30°	436.6	29.5
30°-40°	424.8	28.7
40°-50°	212.2	14.3
50°-60°	32.9	2.2
60°-70°	4.0	0.3
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	805.1	54.4
0°-40°	1229.9	83.1
0°-60°	1474.9	99.7
0°-90°	1480.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1480.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	907	
5°	919	89
15°	988	280
25°	959	437
35°	690	425
45°	266	212
55°	27	33
65°	3	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P858437

CATALOG NUMBER: LD4C15W2N2765D010 4LBWLI\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	906.8
2.5°	910.2
5°	918.7
7.5°	932.2
10°	949.2
12.5°	971.2
15°	988.2
17.5°	1001.7
20°	1003.4
22.5°	991.6
25°	959.4
27.5°	911.9
30°	852.6
32.5°	778.0
35°	689.9
37.5°	593.2
40°	491.5
42.5°	383.1
45°	266.1
47.5°	171.2
50°	103.4
52.5°	55.9
55°	27.2
57.5°	11.9
60°	6.8
62.5°	5.1
65°	3.4
67.5°	3.4
70°	1.7
72.5°	1.7
75°	1.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)