

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858815

Luminaire Tested: **LX4C05D010 EX4C059035 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P858815
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C05D010 EX4C059035 4LBSH
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 651.0 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858815

CATALOG NUMBER: LX4C05D010 EX4C059035 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P858815

CATALOG NUMBER: LX4C05D010 EX4C059035 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99 | 101 | 98 | 96 | 97 | 95 | 93 | 93 | 92 | 90 | 88 | | | |
| 2 | 102 | 96 | 90 | 85 | 100 | 94 | 88 | 84 | 90 | 86 | 82 | 87 | 83 | 80 | 84 | 81 | 79 | 77 | | | |
| 3 | 95 | 85 | 78 | 73 | 92 | 84 | 77 | 72 | 81 | 75 | 71 | 78 | 74 | 70 | 76 | 72 | 69 | 67 | | | |
| 4 | 87 | 77 | 69 | 63 | 85 | 75 | 68 | 63 | 73 | 67 | 62 | 71 | 65 | 61 | 69 | 64 | 60 | 58 | | | |
| 5 | 81 | 69 | 61 | 55 | 79 | 68 | 61 | 55 | 66 | 60 | 55 | 64 | 59 | 54 | 63 | 58 | 53 | 51 | | | |
| 6 | 75 | 63 | 55 | 49 | 73 | 62 | 54 | 49 | 60 | 54 | 49 | 59 | 53 | 48 | 57 | 52 | 48 | 46 | | | |
| 7 | 70 | 58 | 50 | 44 | 68 | 57 | 49 | 44 | 55 | 49 | 44 | 54 | 48 | 43 | 53 | 47 | 43 | 41 | | | |
| 8 | 65 | 53 | 45 | 40 | 64 | 52 | 45 | 40 | 51 | 44 | 39 | 50 | 44 | 39 | 49 | 43 | 39 | 37 | | | |
| 9 | 61 | 49 | 41 | 36 | 60 | 48 | 41 | 36 | 47 | 40 | 36 | 46 | 40 | 36 | 45 | 40 | 35 | 34 | | | |
| 10 | 58 | 45 | 38 | 33 | 56 | 45 | 38 | 33 | 44 | 37 | 33 | 43 | 37 | 33 | 42 | 37 | 33 | 31 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 41832 |
| 5° | 41634 |
| 10° | 40780 |
| 15° | 39288 |
| 20° | 37483 |
| 25° | 35461 |
| 30° | 33450 |
| 35° | 31495 |
| 40° | 29653 |
| 45° | 27642 |
| 50° | 25210 |
| 55° | 22254 |
| 60° | 18846 |
| 65° | 14796 |
| 70° | 10560 |
| 75° | 5791 |
| 80° | 990 |
| 85° | 0 |



TEST NUMBER: P858815

CATALOG NUMBER: LX4C05D010 EX4C059035 4LSBH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 31.9 | 4.9 |
| 10°-20° | 86.7 | 13.3 |
| 20°-30° | 120.4 | 18.5 |
| 30°-40° | 131.4 | 20.2 |
| 40°-50° | 122.5 | 18.8 |
| 50°-60° | 93.0 | 14.3 |
| 60°-70° | 50.9 | 7.8 |
| 70°-80° | 14.0 | 2.2 |
| 80°-90° | 0.2 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 238.9 | 36.7 |
| 0°-40° | 370.3 | 56.9 |
| 0°-60° | 585.8 | 90.0 |
| 0°-90° | 651.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 651.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 340 | |
| 5° | 338 | 32 |
| 15° | 309 | 87 |
| 25° | 262 | 120 |
| 35° | 210 | 131 |
| 45° | 159 | 123 |
| 55° | 104 | 93 |
| 65° | 51 | 51 |
| 75° | 12 | 14 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P858815

CATALOG NUMBER: LX4C05D010 EX4C059035 4LBSH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 340.5 |
| 2.5° | 340.5 |
| 5° | 337.6 |
| 7.5° | 333.3 |
| 10° | 326.9 |
| 12.5° | 318.3 |
| 15° | 308.9 |
| 17.5° | 297.5 |
| 20° | 286.7 |
| 22.5° | 273.8 |
| 25° | 261.6 |
| 27.5° | 249.4 |
| 30° | 235.8 |
| 32.5° | 222.9 |
| 35° | 210.0 |
| 37.5° | 197.1 |
| 40° | 184.9 |
| 42.5° | 172.0 |
| 45° | 159.1 |
| 47.5° | 146.2 |
| 50° | 131.9 |
| 52.5° | 118.3 |
| 55° | 103.9 |
| 57.5° | 90.3 |
| 60° | 76.7 |
| 62.5° | 63.1 |
| 65° | 50.9 |
| 67.5° | 39.4 |
| 70° | 29.4 |
| 72.5° | 20.1 |
| 75° | 12.2 |
| 77.5° | 5.7 |
| 80° | 1.4 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)