

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858129

Luminaire Tested: **LX4C45D010 EX4C459030 4LBMH**

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-08
Report Number: P858129
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459030 4LBMH
Description: 4 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3504.0 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858129

CATALOG NUMBER: LX4C45D010 EX4C459030 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P858129

CATALOG NUMBER: LX4C45D010 EX4C459030 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	277465
5°	278524
10°	279375
15°	279392
20°	277857
25°	271338
30°	253615
35°	219625
40°	171568
45°	123096
50°	79967
55°	47871
60°	28011
65°	17994
70°	11961
75°	9019
80°	6721
85°	0



TEST NUMBER: P858129

CATALOG NUMBER: LX4C45D010 EX4C459030 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.1	6.1
10°-20°	619.7	17.7
20°-30°	914.5	26.1
30°-40°	902.5	25.8
40°-50°	552.3	15.8
50°-60°	211.7	6.0
60°-70°	66.2	1.9
70°-80°	19.4	0.6
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1749.3	49.9
0°-40°	2651.8	75.7
0°-60°	3415.8	97.5
0°-90°	3504.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3504.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2258	
5°	2258	215
15°	2197	620
25°	2002	915
35°	1464	902
45°	708	552
55°	224	212
65°	62	66
75°	19	19
85°	0	3
90°	0	



TEST NUMBER: P858129

CATALOG NUMBER: LX4C45D010 EX4C459030 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2258.5
2.5°	2263.3
5°	2258.5
7.5°	2253.8
10°	2239.5
12.5°	2220.5
15°	2196.7
17.5°	2168.1
20°	2125.3
22.5°	2077.9
25°	2001.7
27.5°	1906.6
30°	1787.8
32.5°	1640.5
35°	1464.4
37.5°	1269.5
40°	1069.8
42.5°	884.4
45°	708.5
47.5°	551.4
50°	418.4
52.5°	309.1
55°	223.5
57.5°	156.8
60°	114.0
62.5°	85.7
65°	61.9
67.5°	47.6
70°	33.3
72.5°	23.8
75°	19.0
77.5°	9.5
80°	9.5
82.5°	4.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)