

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858835

Luminaire Tested: **LD4C05D010 EU4059050 4LBHYH**

Issue Date: 10/18/2023

Test Information

Test Method: LM-79-08
Report Number: P858835
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-7)
Test Lab: INNOVATION CENTER
Issue Date: 10/18/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C05D010 EU4059050 4LBHYH
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 4LCHYP TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 411.8 lumens
Efficiency: N/A
Efficacy: 57.2 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.59
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858835

CATALOG NUMBER: LD4C05D010 EU4059050 4LBHYH

Luminous Intensity Polar Plot





TEST NUMBER: P858835

CATALOG NUMBER: LD4C05D010 EU4059050 4LBHYH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96	96	96	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92	92	92	92
3	106	101	97	94	105	100	96	93	97	94	92	95	93	91	93	91	89	88	88	88	88
4	103	97	92	89	101	96	92	88	94	90	87	92	89	86	90	87	86	84	84	84	84
5	99	92	88	84	97	92	87	84	90	86	83	88	85	83	87	84	82	81	81	81	81
6	95	89	84	81	94	88	83	80	86	83	80	85	82	79	84	81	79	78	78	78	78
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	75	75	75	75
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72	72	72	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	69	69
10	83	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	68	67	67	67	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132461
5°	128971
10°	111900
15°	86335
20°	60166
25°	31692
30°	8866
35°	3914
40°	1957
45°	1008
50°	440
55°	64
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858835

CATALOG NUMBER: LD4C05D010 EU4059050 4LBHYH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.9	23.0
10°-20°	185.6	45.1
20°-30°	107.2	26.0
30°-40°	18.8	4.6
40°-50°	4.8	1.2
50°-60°	0.5	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	387.7	94.1
0°-40°	406.5	98.7
0°-60°	411.8	100.0
0°-90°	411.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	411.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1078	
5°	1046	95
15°	679	186
25°	234	107
35°	26	19
45°	6	5
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858835

CATALOG NUMBER: LD4C05D010 EU4059050 4LBHYH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1078.2
2.5°	1076.6
5°	1045.8
7.5°	981.5
10°	897.0
12.5°	797.9
15°	678.8
17.5°	556.2
20°	460.2
22.5°	345.6
25°	233.8
27.5°	133.8
30°	62.5
32.5°	42.6
35°	26.1
37.5°	17.6
40°	12.2
42.5°	8.3
45°	5.8
47.5°	3.8
50°	2.3
52.5°	1.0
55°	0.3
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)