

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858171

Luminaire Tested: **LX4C45D010 EX4C459040 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858171
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459040 4LBMH
Description: 4 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3558.0 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858171

CATALOG NUMBER: LX4C45D010 EX4C459040 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P858171

CATALOG NUMBER: LX4C45D010 EX4C459040 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82																			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67																			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61																			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55																			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50																			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43																			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	281740
5°	282816
10°	283679
15°	283691
20°	282132
25°	275527
30°	257517
35°	223000
40°	174214
45°	124989
50°	81190
55°	48599
60°	28453
65°	18256
70°	12141
75°	9161
80°	6863
85°	0



TEST NUMBER: P858171

CATALOG NUMBER: LX4C45D010 EX4C459040 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.4	6.1
10°-20°	629.3	17.7
20°-30°	928.6	26.1
30°-40°	916.4	25.8
40°-50°	560.8	15.8
50°-60°	215.0	6.0
60°-70°	67.2	1.9
70°-80°	19.7	0.6
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1776.3	49.9
0°-40°	2692.6	75.7
0°-60°	3468.4	97.5
0°-90°	3558.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3558.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2293	
5°	2293	218
15°	2230	629
25°	2033	929
35°	1487	916
45°	719	561
55°	227	215
65°	63	67
75°	19	20
85°	0	3
90°	0	



TEST NUMBER: P858171

CATALOG NUMBER: LX4C45D010 EX4C459040 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2293.3
2.5°	2298.2
5°	2293.3
7.5°	2288.5
10°	2274.0
12.5°	2254.7
15°	2230.5
17.5°	2201.5
20°	2158.0
22.5°	2109.9
25°	2032.6
27.5°	1935.9
30°	1815.3
32.5°	1665.7
35°	1486.9
37.5°	1289.0
40°	1086.3
42.5°	898.0
45°	719.4
47.5°	559.9
50°	424.8
52.5°	313.9
55°	226.9
57.5°	159.3
60°	115.8
62.5°	87.0
65°	62.8
67.5°	48.3
70°	33.8
72.5°	24.2
75°	19.3
77.5°	9.7
80°	9.7
82.5°	4.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)