

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858859

Luminaire Tested: **LX4C05D010 EX4C059827 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P858859
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C05D010 EX4C059827 4LBMDLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 463.7 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858859

CATALOG NUMBER: LX4C05D010 EX4C059827 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P858859

CATALOG NUMBER: LX4C05D010 EX4C059827 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	66	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	63	59	57	55			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74830
5°	77373
10°	78155
15°	70398
20°	58518
25°	45899
30°	33592
35°	17352
40°	8243
45°	2901
50°	650
55°	428
60°	295
65°	233
70°	144
75°	95
80°	71
85°	0



TEST NUMBER: P858859

CATALOG NUMBER: LX4C05D010 EX4C059827 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.9	12.9
10°-20°	152.5	32.9
20°-30°	154.3	33.3
30°-40°	78.6	17.0
40°-50°	15.4	3.3
50°-60°	1.9	0.4
60°-70°	0.8	0.2
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	366.7	79.1
0°-40°	445.3	96.0
0°-60°	462.6	99.8
0°-90°	463.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	463.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	609	
5°	627	60
15°	554	152
25°	339	154
35°	116	79
45°	17	15
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858859

CATALOG NUMBER: LX4C05D010 EX4C059827 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	609.1
2.5°	614.7
5°	627.4
7.5°	634.7
10°	626.5
12.5°	599.0
15°	553.5
17.5°	499.9
20°	447.6
22.5°	393.3
25°	338.6
27.5°	284.2
30°	236.8
32.5°	178.4
35°	115.7
37.5°	77.5
40°	51.4
42.5°	32.3
45°	16.7
47.5°	6.0
50°	3.4
52.5°	2.6
55°	2.0
57.5°	1.5
60°	1.2
62.5°	1.0
65°	0.8
67.5°	0.5
70°	0.4
72.5°	0.4
75°	0.2
77.5°	0.2
80°	0.1
82.5°	0.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)