

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858864

Luminaire Tested: **LX4C05D010 EX4C059827 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P858864
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C05D010 EX4C059827 4LBSH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 551.1 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858864

CATALOG NUMBER: LX4C05D010 EX4C059827 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P858864

CATALOG NUMBER: LX4C05D010 EX4C059827 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35406
5°	35246
10°	34518
15°	33259
20°	31730
25°	30025
30°	28329
35°	26666
40°	25099
45°	23403
50°	21330
55°	18849
60°	15946
65°	12529
70°	8944
75°	4889
80°	849
85°	0



TEST NUMBER: P858864

CATALOG NUMBER: LX4C05D010 EX4C059827 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.0	4.9
10°-20°	73.4	13.3
20°-30°	101.9	18.5
30°-40°	111.2	20.2
40°-50°	103.7	18.8
50°-60°	78.7	14.3
60°-70°	43.1	7.8
70°-80°	11.8	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	202.3	36.7
0°-40°	313.5	56.9
0°-60°	495.9	90.0
0°-90°	551.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	551.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	288	
5°	286	27
15°	262	73
25°	222	102
35°	178	111
45°	135	104
55°	88	79
65°	43	43
75°	10	12
85°	0	0
90°	0	



TEST NUMBER: P858864

CATALOG NUMBER: LX4C05D010 EX4C059827 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	288.2
2.5°	288.2
5°	285.8
7.5°	282.1
10°	276.7
12.5°	269.4
15°	261.5
17.5°	251.8
20°	242.7
22.5°	231.8
25°	221.5
27.5°	211.2
30°	199.7
32.5°	188.7
35°	177.8
37.5°	166.8
40°	156.5
42.5°	145.6
45°	134.7
47.5°	123.8
50°	111.6
52.5°	100.1
55°	88.0
57.5°	76.4
60°	64.9
62.5°	53.4
65°	43.1
67.5°	33.4
70°	24.9
72.5°	17.0
75°	10.3
77.5°	4.8
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)