

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858213

Luminaire Tested: **LX4C45D010 EX4C459827 4LBNLI**

Issue Date: 1/21/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P858213  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C45D010 EX4C459827 4LBNLI  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2941.8 lumens  
Efficiency: N/A  
Efficacy: 59.3 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 49.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858213

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P858213

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	930075
5°	836979
10°	648843
15°	469626
20°	325171
25°	237070
30°	172245
35°	101924
40°	42868
45°	13378
50°	1739
55°	964
60°	1106
65°	1308
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858213

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	596.6	20.3
10°-20°	1021.4	34.7
20°-30°	811.8	27.6
30°-40°	429.7	14.6
40°-50°	74.0	2.5
50°-60°	5.5	0.2
60°-70°	2.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2429.8	82.6
0°-40°	2859.5	97.2
0°-60°	2939.1	99.9
0°-90°	2941.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2941.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7571	
5°	6787	597
15°	3692	1021
25°	1749	812
35°	680	430
45°	77	74
55°	4	6
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858213

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBNLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7570.6
2.5°	7375.8
5°	6786.9
7.5°	6016.7
10°	5201.2
12.5°	4412.9
15°	3692.4
17.5°	3021.8
20°	2487.2
22.5°	2079.5
25°	1748.9
27.5°	1481.5
30°	1214.2
32.5°	942.4
35°	679.6
37.5°	448.6
40°	267.3
42.5°	154.1
45°	77.0
47.5°	27.2
50°	9.1
52.5°	9.1
55°	4.5
57.5°	4.5
60°	4.5
62.5°	4.5
65°	4.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)