

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858877

Luminaire Tested: **LX4C05D010 EX4C059830 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P858877
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C05D010 EX4C059830 4LBSH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 572.6 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858877

CATALOG NUMBER: LX4C05D010 EX4C059830 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P858877

CATALOG NUMBER: LX4C05D010 EX4C059830 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	48	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	48	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36782
5°	36615
10°	35853
15°	34557
20°	32959
25°	31191
30°	29422
35°	27701
40°	26093
45°	24306
50°	22171
55°	19577
60°	16561
65°	13023
70°	9303
75°	5079
80°	849
85°	0



TEST NUMBER: P858877

CATALOG NUMBER: LX4C05D010 EX4C059830 4LSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.0	4.9
10°-20°	76.2	13.3
20°-30°	105.9	18.5
30°-40°	115.5	20.2
40°-50°	107.8	18.8
50°-60°	81.8	14.3
60°-70°	44.8	7.8
70°-80°	12.3	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	210.1	36.7
0°-40°	325.7	56.9
0°-60°	515.2	90.0
0°-90°	572.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	572.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	299	
5°	297	28
15°	272	76
25°	230	106
35°	185	116
45°	140	108
55°	91	82
65°	45	45
75°	11	12
85°	0	0
90°	0	



TEST NUMBER: P858877

CATALOG NUMBER: LX4C05D010 EX4C059830 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	299.4
2.5°	299.4
5°	296.9
7.5°	293.1
10°	287.4
12.5°	279.9
15°	271.7
17.5°	261.6
20°	252.1
22.5°	240.8
25°	230.1
27.5°	219.4
30°	207.4
32.5°	196.0
35°	184.7
37.5°	173.4
40°	162.7
42.5°	151.2
45°	139.9
47.5°	128.6
50°	116.0
52.5°	104.0
55°	91.4
57.5°	79.5
60°	67.4
62.5°	55.5
65°	44.8
67.5°	34.7
70°	25.9
72.5°	17.7
75°	10.7
77.5°	5.1
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)