

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858214

Luminaire Tested: **LX4C45D010 EX4C459827 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P858214
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459827 4LBSH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3925.4 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858214

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P858214

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	252218
5°	251048
10°	245867
15°	236924
20°	226020
25°	213836
30°	201723
35°	189930
40°	178817
45°	166705
50°	152003
55°	134232
60°	113639
65°	89186
70°	63686
75°	34888
80°	6084
85°	0



TEST NUMBER: P858214

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.3	4.9
10°-20°	522.7	13.3
20°-30°	725.9	18.5
30°-40°	792.1	20.2
40°-50°	738.9	18.8
50°-60°	560.8	14.3
60°-70°	307.1	7.8
70°-80°	84.5	2.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1440.8	36.7
0°-40°	2232.9	56.9
0°-60°	3532.7	90.0
0°-90°	3925.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3925.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2053	
5°	2036	192
15°	1863	523
25°	1578	726
35°	1266	792
45°	960	739
55°	627	561
65°	307	307
75°	74	84
85°	0	1
90°	0	



TEST NUMBER: P858214

CATALOG NUMBER: LX4C45D010 EX4C459827 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2053.0
2.5°	2053.0
5°	2035.7
7.5°	2009.8
10°	1970.9
12.5°	1919.0
15°	1862.8
17.5°	1793.7
20°	1728.8
22.5°	1651.1
25°	1577.5
27.5°	1504.1
30°	1422.0
32.5°	1344.1
35°	1266.4
37.5°	1188.6
40°	1115.0
42.5°	1037.3
45°	959.5
47.5°	881.7
50°	795.3
52.5°	713.1
55°	626.7
57.5°	544.6
60°	462.5
62.5°	380.4
65°	306.8
67.5°	237.6
70°	177.3
72.5°	121.0
75°	73.5
77.5°	34.5
80°	8.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)