

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858225

Luminaire Tested: **LX4C45D010 EX4C459830 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459830 4LBNH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2595.9 lumens
Efficiency: N/A
Efficacy: 52.3 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858225

CATALOG NUMBER: LX4C45D010 EX4C459830 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P858225

CATALOG NUMBER: LX4C45D010 EX4C459830 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	400404
5°	391488
10°	361971
15°	324811
20°	285924
25°	246057
30°	198149
35°	131904
40°	68624
45°	31065
50°	13474
55°	9060
60°	5774
65°	4128
70°	3412
75°	2231
80°	0
85°	0



TEST NUMBER: P858225

CATALOG NUMBER: LX4C45D010 EX4C459830 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.1	11.3
10°-20°	713.3	27.5
20°-30°	828.1	31.9
30°-40°	548.4	21.1
40°-50°	153.8	5.9
50°-60°	38.6	1.5
60°-70°	14.6	0.6
70°-80°	5.0	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1835.5	70.7
0°-40°	2383.9	91.8
0°-60°	2576.4	99.2
0°-90°	2595.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2595.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3259	
5°	3174	294
15°	2554	713
25°	1815	828
35°	880	548
45°	179	154
55°	42	39
65°	14	15
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P858225

CATALOG NUMBER: LX4C45D010 EX4C459830 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3259.2
2.5°	3245.0
5°	3174.5
7.5°	3052.2
10°	2901.6
12.5°	2732.3
15°	2553.8
17.5°	2379.7
20°	2187.0
22.5°	2008.2
25°	1815.2
27.5°	1632.0
30°	1396.8
32.5°	1147.5
35°	879.5
37.5°	630.2
40°	427.9
42.5°	277.4
45°	178.8
47.5°	108.3
50°	70.5
52.5°	51.6
55°	42.3
57.5°	33.0
60°	23.5
62.5°	18.9
65°	14.2
67.5°	9.5
70°	9.5
72.5°	4.7
75°	4.7
77.5°	4.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)