

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858888

Luminaire Tested: **LX4C05D010 EX4C059835 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858888
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C05D010 EX4C059835 4LBNH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 369.2 lumens
Efficiency: N/A
Efficacy: 51.3 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858888

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P858888

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70
6	88	79	73	69	86	78	72	68	76	72	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56943
5°	55680
10°	51484
15°	46194
20°	40659
25°	35000
30°	28187
35°	18762
40°	9751
45°	4413
50°	1911
55°	1285
60°	835
65°	610
70°	467
75°	332
80°	0
85°	0



TEST NUMBER: P858888

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.8	11.3
10°-20°	101.4	27.5
20°-30°	117.8	31.9
30°-40°	78.0	21.1
40°-50°	21.9	5.9
50°-60°	5.5	1.5
60°-70°	2.1	0.6
70°-80°	0.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	261.0	70.7
0°-40°	339.0	91.8
0°-60°	366.4	99.2
0°-90°	369.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	369.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	464	
5°	452	42
15°	363	101
25°	258	118
35°	125	78
45°	25	22
55°	6	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P858888

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	463.5
2.5°	461.5
5°	451.5
7.5°	434.1
10°	412.7
12.5°	388.6
15°	363.2
17.5°	338.4
20°	311.0
22.5°	285.6
25°	258.2
27.5°	232.1
30°	198.7
32.5°	163.2
35°	125.1
37.5°	89.6
40°	60.8
42.5°	39.4
45°	25.4
47.5°	15.4
50°	10.0
52.5°	7.3
55°	6.0
57.5°	4.7
60°	3.4
62.5°	2.7
65°	2.1
67.5°	1.3
70°	1.3
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)