

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858912

Luminaire Tested: **LX4C05D010 EX4C059850 4LBMH**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P858912  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C05D010 EX4C059850 4LBMH  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 454.7 lumens  
Efficiency: N/A  
Efficacy: 63.2 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858912

CATALOG NUMBER: LX4C05D010 EX4C059850 4LBMH

### Luminous Intensity Polar Plot





TEST NUMBER: P858912

CATALOG NUMBER: LX4C05D010 EX4C059850 4LBMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  | 99  | 97  | 96  | 96  | 94  | 93  | 91  |    |    |   |
| 2   | 105 | 100 | 95  | 91  | 103 | 98  | 93  | 90  | 95  | 91  | 88  | 91  | 88  | 86  | 89  | 86  | 84  | 82  |    |    |   |
| 3   | 99  | 91  | 85  | 80  | 97  | 90  | 84  | 80  | 87  | 82  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 74  |    |    |   |
| 4   | 92  | 83  | 77  | 72  | 90  | 82  | 76  | 71  | 80  | 75  | 70  | 78  | 73  | 70  | 76  | 72  | 69  | 67  |    |    |   |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 69  | 64  | 74  | 68  | 64  | 72  | 67  | 63  | 70  | 66  | 62  | 61  |    |    |   |
| 6   | 81  | 71  | 64  | 58  | 80  | 70  | 63  | 58  | 68  | 62  | 58  | 67  | 61  | 57  | 65  | 61  | 57  | 55  |    |    |   |
| 7   | 76  | 65  | 58  | 53  | 75  | 65  | 58  | 53  | 63  | 57  | 53  | 62  | 56  | 52  | 61  | 56  | 52  | 50  |    |    |   |
| 8   | 72  | 60  | 53  | 49  | 70  | 60  | 53  | 49  | 59  | 53  | 48  | 58  | 52  | 48  | 57  | 52  | 48  | 46  |    |    |   |
| 9   | 68  | 56  | 49  | 45  | 66  | 56  | 49  | 45  | 55  | 49  | 44  | 54  | 48  | 44  | 53  | 48  | 44  | 43  |    |    |   |
| 10  | 64  | 52  | 46  | 41  | 63  | 52  | 46  | 41  | 51  | 45  | 41  | 50  | 45  | 41  | 49  | 44  | 41  | 39  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 36008 |
| 5°  | 36146 |
| 10° | 36264 |
| 15° | 36261 |
| 20° | 36058 |
| 25° | 35230 |
| 30° | 32911 |
| 35° | 28496 |
| 40° | 22260 |
| 45° | 15967 |
| 50° | 10378 |
| 55° | 6211  |
| 60° | 3636  |
| 65° | 2326  |
| 70° | 1545  |
| 75° | 1187  |
| 80° | 849   |
| 85° | 0     |



TEST NUMBER: P858912

CATALOG NUMBER: LX4C05D010 EX4C059850 4LBMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 27.9   | 6.1       |
| 10°-20°   | 80.4   | 17.7      |
| 20°-30°   | 118.7  | 26.1      |
| 30°-40°   | 117.1  | 25.8      |
| 40°-50°   | 71.7   | 15.8      |
| 50°-60°   | 27.5   | 6.0       |
| 60°-70°   | 8.6    | 1.9       |
| 70°-80°   | 2.5    | 0.6       |
| 80°-90°   | 0.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 227.1  | 49.9      |
| 0°-40°    | 344.2  | 75.7      |
| 0°-60°    | 443.3  | 97.5      |
| 0°-90°    | 454.7  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 454.7  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 293 |      |
| 5°  | 293 | 28   |
| 15° | 285 | 80   |
| 25° | 260 | 119  |
| 35° | 190 | 117  |
| 45° | 92  | 72   |
| 55° | 29  | 27   |
| 65° | 8   | 9    |
| 75° | 2   | 3    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P858912

CATALOG NUMBER: LX4C05D010 EX4C059850 4LBMH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 293.1 |
| 2.5°  | 293.7 |
| 5°    | 293.1 |
| 7.5°  | 292.5 |
| 10°   | 290.7 |
| 12.5° | 288.2 |
| 15°   | 285.1 |
| 17.5° | 281.4 |
| 20°   | 275.8 |
| 22.5° | 269.7 |
| 25°   | 259.9 |
| 27.5° | 247.5 |
| 30°   | 232.0 |
| 32.5° | 212.9 |
| 35°   | 190.0 |
| 37.5° | 164.8 |
| 40°   | 138.8 |
| 42.5° | 114.8 |
| 45°   | 91.9  |
| 47.5° | 71.6  |
| 50°   | 54.3  |
| 52.5° | 40.1  |
| 55°   | 29.0  |
| 57.5° | 20.3  |
| 60°   | 14.8  |
| 62.5° | 11.1  |
| 65°   | 8.0   |
| 67.5° | 6.2   |
| 70°   | 4.3   |
| 72.5° | 3.1   |
| 75°   | 2.5   |
| 77.5° | 1.2   |
| 80°   | 1.2   |
| 82.5° | 0.6   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)