

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858261

Luminaire Tested: **LX4C45D010 EX4C459850 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P858261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459850 4LBMDLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3558.1 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858261

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P858261

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	79	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	66	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	63	59	57	55			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	574131
5°	593688
10°	599704
15°	540215
20°	448941
25°	352223
30°	257758
35°	133209
40°	63251
45°	22256
50°	5027
55°	3256
60°	2310
65°	1744
70°	1221
75°	807
80°	637
85°	0



TEST NUMBER: P858261

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	459.8	12.9
10°-20°	1169.9	32.9
20°-30°	1183.8	33.3
30°-40°	603.5	17.0
40°-50°	118.3	3.3
50°-60°	14.3	0.4
60°-70°	6.0	0.2
70°-80°	2.1	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2813.5	79.1
0°-40°	3417.0	96.0
0°-60°	3549.6	99.8
0°-90°	3558.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3558.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4673	
5°	4814	460
15°	4247	1170
25°	2598	1184
35°	888	603
45°	128	118
55°	15	14
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P858261

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4673.3
2.5°	4716.5
5°	4814.1
7.5°	4870.1
10°	4807.3
12.5°	4596.0
15°	4247.4
17.5°	3836.0
20°	3433.9
22.5°	3017.4
25°	2598.4
27.5°	2180.9
30°	1817.0
32.5°	1369.2
35°	888.2
37.5°	594.6
40°	394.4
42.5°	247.7
45°	128.1
47.5°	45.8
50°	26.3
52.5°	19.5
55°	15.2
57.5°	11.9
60°	9.4
62.5°	7.7
65°	6.0
67.5°	4.3
70°	3.4
72.5°	2.6
75°	1.7
77.5°	1.7
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)