

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858264

Luminaire Tested: **LX4C45D010 EX4C459850 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459850 4LBNH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2690.4 lumens
Efficiency: N/A
Efficacy: 54.2 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858264

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P858264

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	414987
5°	405757
10°	375157
15°	336627
20°	296331
25°	255017
30°	205369
35°	136703
40°	71126
45°	32194
50°	13971
55°	9381
60°	5995
65°	4244
70°	3520
75°	2326
80°	0
85°	0



TEST NUMBER: P858264

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.8	11.3
10°-20°	739.3	27.5
20°-30°	858.3	31.9
30°-40°	568.4	21.1
40°-50°	159.4	5.9
50°-60°	40.0	1.5
60°-70°	15.0	0.6
70°-80°	5.2	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1902.3	70.7
0°-40°	2470.7	91.8
0°-60°	2670.2	99.2
0°-90°	2690.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2690.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3378	
5°	3290	305
15°	2647	739
25°	1881	858
35°	912	568
45°	185	159
55°	44	40
65°	15	15
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P858264

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3377.9
2.5°	3363.2
5°	3290.2
7.5°	3163.3
10°	3007.3
12.5°	2831.8
15°	2646.7
17.5°	2466.3
20°	2266.6
22.5°	2081.3
25°	1881.3
27.5°	1691.4
30°	1447.7
32.5°	1189.3
35°	911.5
37.5°	653.2
40°	443.5
42.5°	287.5
45°	185.3
47.5°	112.2
50°	73.1
52.5°	53.5
55°	43.8
57.5°	34.2
60°	24.4
62.5°	19.5
65°	14.6
67.5°	9.8
70°	9.8
72.5°	4.9
75°	4.9
77.5°	4.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)