

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858269

Luminaire Tested: **LX4C45D010 EX4C459850 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858269
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C45D010 EX4C459850 4LBWH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3599.0 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858269

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P858269

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82																			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67																			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61																			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55																			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50																			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43																			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	284995
5°	286084
10°	286947
15°	286973
20°	285388
25°	278712
30°	260496
35°	225580
40°	176219
45°	126449
50°	82127
55°	49156
60°	28772
65°	18488
70°	12285
75°	9256
80°	6933
85°	0



TEST NUMBER: P858269

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.9	6.1
10°-20°	636.6	17.7
20°-30°	939.3	26.1
30°-40°	926.9	25.8
40°-50°	567.3	15.8
50°-60°	217.5	6.0
60°-70°	68.0	1.9
70°-80°	19.9	0.6
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1796.8	49.9
0°-40°	2723.7	75.7
0°-60°	3508.5	97.5
0°-90°	3599.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3599.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2320	
5°	2320	221
15°	2256	637
25°	2056	939
35°	1504	927
45°	728	567
55°	230	217
65°	64	68
75°	20	20
85°	0	3
90°	0	



TEST NUMBER: P858269

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2319.8
2.5°	2324.7
5°	2319.8
7.5°	2315.0
10°	2300.2
12.5°	2280.7
15°	2256.3
17.5°	2226.9
20°	2182.9
22.5°	2134.3
25°	2056.1
27.5°	1958.3
30°	1836.3
32.5°	1684.9
35°	1504.1
37.5°	1303.9
40°	1098.8
42.5°	908.3
45°	727.8
47.5°	566.4
50°	429.7
52.5°	317.5
55°	229.5
57.5°	161.1
60°	117.1
62.5°	88.0
65°	63.6
67.5°	48.9
70°	34.2
72.5°	24.4
75°	19.5
77.5°	9.8
80°	9.8
82.5°	4.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)