

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858270

Luminaire Tested: **LX4C45D010 EX4C459850 4LBWLI**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P858270  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C45D010 EX4C459850 4LBWLI  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4263.4 lumens  
Efficiency: N/A  
Efficacy: 86.0 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct  
  
Input Watts (W): 49.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858270

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P858270

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P858270

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	255.5	6.0
10°-20°	806.2	18.9
20°-30°	1257.6	29.5
30°-40°	1223.7	28.7
40°-50°	611.2	14.3
50°-60°	94.6	2.2
60°-70°	11.4	0.3
70°-80°	3.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2319.3	54.4
0°-40°	3542.9	83.1
0°-60°	4248.7	99.7
0°-90°	4263.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4263.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2612	
5°	2646	255
15°	2847	806
25°	2764	1258
35°	1987	1224
45°	767	611
55°	78	95
65°	10	11
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P858270

CATALOG NUMBER: LX4C45D010 EX4C459850 4LBWLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2612.2
2.5°	2622.0
5°	2646.4
7.5°	2685.5
10°	2734.4
12.5°	2797.8
15°	2846.6
17.5°	2885.8
20°	2890.6
22.5°	2856.4
25°	2763.7
27.5°	2626.8
30°	2455.9
32.5°	2241.3
35°	1987.3
37.5°	1708.8
40°	1416.0
42.5°	1103.5
45°	766.6
47.5°	493.1
50°	297.8
52.5°	161.1
55°	78.2
57.5°	34.2
60°	19.5
62.5°	14.6
65°	9.8
67.5°	9.8
70°	4.9
72.5°	4.9
75°	4.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)