

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858288

Luminaire Tested: **LD4C10W2N2050D010 4LBNH_5000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10W2N2050D010 4LBNH_5000K
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2050 LEDS AND 4LBNH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 682.1 lumens
Efficiency: N/A
Efficacy: 52.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858288

CATALOG NUMBER: LD4C10W2N2050D010 4LBNH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P858288

CATALOG NUMBER: LD4C10W2N2050D010 4LBNH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	76	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107411
5°	104750
10°	96655
15°	85572
20°	74298
25°	63548
30°	52389
35°	34510
40°	18555
45°	8218
50°	3326
55°	2399
60°	1523
65°	1105
70°	898
75°	617
80°	920
85°	0



TEST NUMBER: P858288

CATALOG NUMBER: LD4C10W2N2050D010 4LBNH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.6	11.5
10°-20°	187.5	27.5
20°-30°	214.8	31.5
30°-40°	144.3	21.2
40°-50°	41.2	6.0
50°-60°	10.1	1.5
60°-70°	3.9	0.6
70°-80°	1.5	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	480.9	70.5
0°-40°	625.2	91.7
0°-60°	676.5	99.2
0°-90°	682.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	682.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	874	
5°	849	79
15°	673	187
25°	469	215
35°	230	144
45°	47	41
55°	11	10
65°	4	4
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P858288

CATALOG NUMBER: LD4C10W2N2050D010 4LBNH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	874.3
2.5°	868.0
5°	849.4
7.5°	815.8
10°	774.8
12.5°	722.5
15°	672.8
17.5°	620.6
20°	568.3
22.5°	518.6
25°	468.8
27.5°	422.8
30°	369.3
32.5°	298.4
35°	230.1
37.5°	167.9
40°	115.7
42.5°	75.9
45°	47.3
47.5°	28.6
50°	17.4
52.5°	13.7
55°	11.2
57.5°	8.7
60°	6.2
62.5°	5.0
65°	3.8
67.5°	2.5
70°	2.5
72.5°	1.3
75°	1.3
77.5°	1.3
80°	1.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)