

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859000

Luminaire Tested: **LX4C50D010 EX4C509035 4LBMH**

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-08
Report Number: P859000
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C50D010 EX4C509035 4LBMH
Description: 4 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4024.0 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859000

CATALOG NUMBER: LX4C50D010 EX4C509035 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P859000

CATALOG NUMBER: LX4C50D010 EX4C509035 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	318645
5°	319862
10°	320829
15°	320855
20°	319092
25°	311611
30°	291251
35°	252215
40°	197019
45°	141356
50°	91836
55°	54961
60°	32163
65°	20668
70°	13757
75°	10395
80°	7712
85°	0



TEST NUMBER: P859000

CATALOG NUMBER: LX4C50D010 EX4C509035 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.0	6.1
10°-20°	711.7	17.7
20°-30°	1050.2	26.1
30°-40°	1036.4	25.8
40°-50°	634.2	15.8
50°-60°	243.1	6.0
60°-70°	76.1	1.9
70°-80°	22.3	0.6
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2008.9	49.9
0°-40°	3045.3	75.7
0°-60°	3922.7	97.5
0°-90°	4024.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4024.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2594	
5°	2594	247
15°	2523	712
25°	2299	1050
35°	1682	1036
45°	814	634
55°	257	243
65°	71	76
75°	22	22
85°	0	3
90°	0	



TEST NUMBER: P859000

CATALOG NUMBER: LX4C50D010 EX4C509035 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2593.7
2.5°	2599.2
5°	2593.7
7.5°	2588.2
10°	2571.8
12.5°	2550.0
15°	2522.7
17.5°	2489.9
20°	2440.7
22.5°	2386.3
25°	2298.8
27.5°	2189.5
30°	2053.1
32.5°	1883.9
35°	1681.7
37.5°	1457.8
40°	1228.5
42.5°	1015.6
45°	813.6
47.5°	633.3
50°	480.5
52.5°	355.0
55°	256.6
57.5°	180.1
60°	130.9
62.5°	98.4
65°	71.1
67.5°	54.7
70°	38.3
72.5°	27.3
75°	21.9
77.5°	10.9
80°	10.9
82.5°	5.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)