

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859037

Luminaire Tested: **LD4C50D010 EU4509050 4LBMLI**

Issue Date: 7/19/2024

Test Information

Test Method: LM-79-08
Report Number: P859037
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 7/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C50D010 EU4509050 4LBMLI
Description: 4 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5131.0 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859037

CATALOG NUMBER: LD4C50D010 EU4509050 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859037

CATALOG NUMBER: LD4C50D010 EU4509050 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	993725
5°	976840
10°	897554
15°	751651
20°	602192
25°	483859
30°	360194
35°	205768
40°	96577
45°	41003
50°	13054
55°	6661
60°	4570
65°	3605
70°	2227
75°	0
80°	0
85°	0



TEST NUMBER: P859037

CATALOG NUMBER: LD4C50D010 EU4509050 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	732.4	14.3
10°-20°	1637.3	31.9
20°-30°	1627.9	31.7
30°-40°	886.5	17.3
40°-50°	204.9	4.0
50°-60°	28.9	0.6
60°-70°	10.7	0.2
70°-80°	2.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3997.6	77.9
0°-40°	4884.1	95.2
0°-60°	5117.8	99.7
0°-90°	5131.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5131.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8089	
5°	7921	732
15°	5910	1637
25°	3570	1628
35°	1372	886
45°	236	205
55°	31	29
65°	12	11
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P859037

CATALOG NUMBER: LD4C50D010 EU4509050 4LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	8088.7
2.5°	8070.1
5°	7921.0
7.5°	7617.0
10°	7194.9
12.5°	6574.1
15°	5909.8
17.5°	5251.8
20°	4606.1
22.5°	4078.5
25°	3569.5
27.5°	3085.3
30°	2539.1
32.5°	1930.7
35°	1372.0
37.5°	924.8
40°	602.2
42.5°	378.6
45°	236.0
47.5°	136.6
50°	68.3
52.5°	37.3
55°	31.1
57.5°	18.6
60°	18.6
62.5°	12.4
65°	12.4
67.5°	6.2
70°	6.2
72.5°	6.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)