

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858301

Luminaire Tested: **LD4C10W2N2050D010 4LBWH_2000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858301
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10W2N2050D010 4LBWH_2000K
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2000K, W2N2050 LEDS AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 761.0 lumens
Efficiency: N/A
Efficacy: 58.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858301

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH_2000K

Luminous Intensity Polar Plot





TEST NUMBER: P858301

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH_2000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82				82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61				61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55				55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50				50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43				43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39				39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60260
5°	60490
10°	60678
15°	60681
20°	60349
25°	58925
30°	55084
35°	47692
40°	37255
45°	26739
50°	17373
55°	10388
60°	6094
65°	3895
70°	2586
75°	1946
80°	1486
85°	0



TEST NUMBER: P858301

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH_2000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	6.1
10°-20°	134.6	17.7
20°-30°	198.6	26.1
30°-40°	196.0	25.8
40°-50°	120.0	15.8
50°-60°	46.0	6.0
60°-70°	14.4	1.9
70°-80°	4.2	0.6
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.9	49.9
0°-40°	575.9	75.7
0°-60°	741.9	97.5
0°-90°	761.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	761.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	490	
5°	490	47
15°	477	135
25°	435	199
35°	318	196
45°	154	120
55°	48	46
65°	13	14
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P858301

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH_2000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	490.5
2.5°	491.5
5°	490.5
7.5°	489.5
10°	486.4
12.5°	482.2
15°	477.1
17.5°	470.9
20°	461.6
22.5°	451.3
25°	434.7
27.5°	414.1
30°	388.3
32.5°	356.3
35°	318.0
37.5°	275.7
40°	232.3
42.5°	192.1
45°	153.9
47.5°	119.8
50°	90.9
52.5°	67.1
55°	48.5
57.5°	34.1
60°	24.8
62.5°	18.6
65°	13.4
67.5°	10.3
70°	7.2
72.5°	5.2
75°	4.1
77.5°	2.1
80°	2.1
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)