

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858303

Luminaire Tested: **LD4C10W2N2050D010 4LBWH_3000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858303
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10W2N2050D010 4LBWH_3000K
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, W2N2050 LEDS AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 922.0 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858303

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P858303

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82				82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61				61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55				55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50				50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43				43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39				39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73012
5°	73291
10°	73514
15°	73514
20°	73109
25°	71396
30°	66730
35°	57786
40°	45145
45°	32385
50°	21043
55°	12594
60°	7371
65°	4738
70°	3161
75°	2373
80°	1769
85°	0



TEST NUMBER: P858303

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.6	6.1
10°-20°	163.1	17.7
20°-30°	240.6	26.1
30°-40°	237.5	25.8
40°-50°	145.3	15.8
50°-60°	55.7	6.0
60°-70°	17.4	1.9
70°-80°	5.1	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	460.3	49.9
0°-40°	697.8	75.7
0°-60°	898.8	97.5
0°-90°	922.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	922.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	594	
5°	594	57
15°	578	163
25°	527	241
35°	385	237
45°	186	145
55°	59	56
65°	16	17
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P858303

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	594.3
2.5°	595.5
5°	594.3
7.5°	593.0
10°	589.3
12.5°	584.3
15°	578.0
17.5°	570.5
20°	559.2
22.5°	546.8
25°	526.7
27.5°	501.7
30°	470.4
32.5°	431.7
35°	385.3
37.5°	334.0
40°	281.5
42.5°	232.7
45°	186.4
47.5°	145.1
50°	110.1
52.5°	81.3
55°	58.8
57.5°	41.3
60°	30.0
62.5°	22.5
65°	16.3
67.5°	12.5
70°	8.8
72.5°	6.3
75°	5.0
77.5°	2.5
80°	2.5
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)