

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858305

Luminaire Tested: **LD4C10W2N2050D010 4LBWH\_4000K**

Issue Date: 11/9/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P858305  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 11/9/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C10W2N2050D010 4LBWH\_4000K  
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, W2N2050 LEDS AND 4LBWH TRIM WITH FINISH  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 878.0 lumens  
Efficiency: N/A  
Efficacy: 67.5 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 13  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858305

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P858305

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	69523
5°	69788
10°	70009
15°	70004
20°	69618
25°	67994
30°	63553
35°	55026
40°	42996
45°	30839
50°	20030
55°	11995
60°	7027
65°	4506
70°	2981
75°	2278
80°	1698
85°	0



TEST NUMBER: P858305

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.9	6.1
10°-20°	155.3	17.7
20°-30°	229.2	26.1
30°-40°	226.1	25.8
40°-50°	138.4	15.8
50°-60°	53.1	6.0
60°-70°	16.6	1.9
70°-80°	4.9	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	438.3	49.9
0°-40°	664.5	75.7
0°-60°	855.9	97.5
0°-90°	878.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	878.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	566	
5°	566	54
15°	550	155
25°	502	229
35°	367	226
45°	178	138
55°	56	53
65°	16	17
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P858305

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	565.9
2.5°	567.1
5°	565.9
7.5°	564.7
10°	561.2
12.5°	556.4
15°	550.4
17.5°	543.3
20°	532.5
22.5°	520.7
25°	501.6
27.5°	477.7
30°	448.0
32.5°	411.1
35°	366.9
37.5°	318.1
40°	268.1
42.5°	221.6
45°	177.5
47.5°	138.2
50°	104.8
52.5°	77.5
55°	56.0
57.5°	39.3
60°	28.6
62.5°	21.5
65°	15.5
67.5°	11.9
70°	8.3
72.5°	6.0
75°	4.8
77.5°	2.4
80°	2.4
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)