

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858306

Luminaire Tested: **LD4C10W2N2050D010 4LBWH_5000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858306
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10W2N2050D010 4LBWH_5000K
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2050 LEDS AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 912.0 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858306

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P858306

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72213
5°	72489
10°	72716
15°	72713
20°	72324
25°	70624
30°	66007
35°	57156
40°	44648
45°	32038
50°	20814
55°	12466
60°	7297
65°	4680
70°	3125
75°	2373
80°	1769
85°	0



TEST NUMBER: P858306

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.0	6.1
10°-20°	161.3	17.7
20°-30°	238.0	26.1
30°-40°	234.9	25.8
40°-50°	143.7	15.8
50°-60°	55.1	6.0
60°-70°	17.2	1.9
70°-80°	5.1	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	455.3	49.9
0°-40°	690.2	75.7
0°-60°	889.0	97.5
0°-90°	912.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	912.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	588	
5°	588	56
15°	572	161
25°	521	238
35°	381	235
45°	184	144
55°	58	55
65°	16	17
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P858306

CATALOG NUMBER: LD4C10W2N2050D010 4LBWH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	587.8
2.5°	589.1
5°	587.8
7.5°	586.6
10°	582.9
12.5°	577.9
15°	571.7
17.5°	564.3
20°	553.2
22.5°	540.8
25°	521.0
27.5°	496.2
30°	465.3
32.5°	427.0
35°	381.1
37.5°	330.4
40°	278.4
42.5°	230.2
45°	184.4
47.5°	143.5
50°	108.9
52.5°	80.5
55°	58.2
57.5°	40.8
60°	29.7
62.5°	22.3
65°	16.1
67.5°	12.4
70°	8.7
72.5°	6.2
75°	5.0
77.5°	2.5
80°	2.5
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)