

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858318

Luminaire Tested: **LD4C10W2N2765D010 4LBMH_6500K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858318
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10W2N2765D010 4LBMH_6500K
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 6500K, W2N2765 LEDS AND 4LBMH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 847.0 lumens
Efficiency: N/A
Efficacy: 65.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858318

CATALOG NUMBER: LD4C10W2N2765D010 4LBMH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P858318

CATALOG NUMBER: LD4C10W2N2765D010 4LBMH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79				79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73				73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67				67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62				62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103185
5°	101680
10°	97429
15°	92020
20°	85895
25°	77971
30°	65099
35°	47168
40°	29525
45°	16870
50°	8792
55°	4926
60°	3145
65°	1860
70°	1365
75°	617
80°	920
85°	0



TEST NUMBER: P858318

CATALOG NUMBER: LD4C10W2N2765D010 4LBMH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.3	9.1
10°-20°	202.7	23.9
20°-30°	260.5	30.8
30°-40°	196.0	23.1
40°-50°	78.7	9.3
50°-60°	22.4	2.6
60°-70°	7.1	0.8
70°-80°	2.0	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	540.6	63.8
0°-40°	736.6	87.0
0°-60°	837.7	98.9
0°-90°	847.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	847.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	840	
5°	824	77
15°	724	203
25°	575	261
35°	314	196
45°	97	79
55°	23	22
65°	6	7
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P858318

CATALOG NUMBER: LD4C10W2N2765D010 4LBMH_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	839.9
2.5°	834.7
5°	824.5
7.5°	805.3
10°	781.0
12.5°	751.7
15°	723.5
17.5°	691.6
20°	657.0
22.5°	620.0
25°	575.2
27.5°	521.5
30°	458.9
32.5°	388.6
35°	314.5
37.5°	245.4
40°	184.1
42.5°	135.5
45°	97.1
47.5°	66.5
50°	46.0
52.5°	32.0
55°	23.0
57.5°	16.6
60°	12.8
62.5°	9.0
65°	6.4
67.5°	5.1
70°	3.8
72.5°	2.6
75°	1.3
77.5°	1.3
80°	1.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)