

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859177

Luminaire Tested: **LX4C60D010 EX4C609027 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P859177
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C60D010 EX4C609027 4LBMDLI
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5069.0 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859177

CATALOG NUMBER: LX4C60D010 EX4C609027 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P859177

CATALOG NUMBER: LX4C60D010 EX4C609027 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	66	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	63	59	57	55			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	817934
5°	845797
10°	854366
15°	769623
20°	639583
25°	501780
30°	367230
35°	189765
40°	90130
45°	31708
50°	7167
55°	4669
60°	3268
65°	2471
70°	1724
75°	1139
80°	849
85°	0



TEST NUMBER: P859177

CATALOG NUMBER: LX4C60D010 EX4C609027 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	655.1	12.9
10°-20°	1666.7	32.9
20°-30°	1686.5	33.3
30°-40°	859.8	17.0
40°-50°	168.6	3.3
50°-60°	20.4	0.4
60°-70°	8.5	0.2
70°-80°	3.0	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4008.3	79.1
0°-40°	4868.1	96.0
0°-60°	5057.0	99.8
0°-90°	5069.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5069.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6658	
5°	6858	655
15°	6051	1667
25°	3702	1687
35°	1265	860
45°	182	169
55°	22	20
65°	8	8
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P859177

CATALOG NUMBER: LX4C60D010 EX4C609027 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6657.8
2.5°	6719.4
5°	6858.4
7.5°	6938.1
10°	6848.7
12.5°	6547.8
15°	6051.1
17.5°	5464.9
20°	4892.1
22.5°	4298.7
25°	3701.7
27.5°	3107.1
30°	2588.7
32.5°	1950.6
35°	1265.3
37.5°	847.2
40°	562.0
42.5°	352.9
45°	182.5
47.5°	65.3
50°	37.5
52.5°	27.8
55°	21.8
57.5°	16.9
60°	13.3
62.5°	10.9
65°	8.5
67.5°	6.0
70°	4.8
72.5°	3.6
75°	2.4
77.5°	2.4
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)