

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859200

Luminaire Tested: **LX4C60D010 EX4C609030 4LBMLI**

Issue Date: 1/26/2022

Test Information

Test Method: LM-79-08
Report Number: P859200
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C60D010 EX4C609030 4LBMLI
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5984.0 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859200

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859200

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1891870
5°	1702483
10°	1319804
15°	955265
20°	661442
25°	482206
30°	350377
35°	207327
40°	87195
45°	27190
50°	3536
55°	1971
60°	2261
65°	2674
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859200

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1213.6	20.3
10°-20°	2077.6	34.7
20°-30°	1651.2	27.6
30°-40°	874.1	14.6
40°-50°	150.6	2.5
50°-60°	11.3	0.2
60°-70°	5.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4942.4	82.6
0°-40°	5816.5	97.2
0°-60°	5978.4	99.9
0°-90°	5984.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5984.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15399	
5°	13805	###
15°	7511	2078
25°	3557	1651
35°	1382	874
45°	156	151
55°	9	11
65°	9	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859200

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	15399.4
2.5°	15002.9
5°	13805.1
7.5°	12238.5
10°	10579.7
12.5°	8976.2
15°	7510.7
17.5°	6146.7
20°	5059.3
22.5°	4229.8
25°	3557.3
27.5°	3013.6
30°	2469.9
32.5°	1916.9
35°	1382.4
37.5°	912.5
40°	543.7
42.5°	313.4
45°	156.5
47.5°	55.4
50°	18.5
52.5°	18.5
55°	9.2
57.5°	9.2
60°	9.2
62.5°	9.2
65°	9.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)