

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858322

Luminaire Tested: **LD4C10W2N2765D010 4LBMLI\_4000K**

Issue Date: 11/9/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P858322  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 11/9/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C10W2N2765D010 4LBMLI\_4000K  
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, W2N2765 LEDS AND 4LBMLI TRIM WITH FINISH  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 986.0 lumens  
Efficiency: N/A  
Efficacy: 75.8 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 13  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858322

CATALOG NUMBER: LD4C10W2N2765D010 4LBMLI\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P858322

CATALOG NUMBER: LD4C10W2N2765D010 4LBMLI\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	190963
5°	187710
10°	172478
15°	144447
20°	115716
25°	92976
30°	69213
35°	39549
40°	18555
45°	7888
50°	2504
55°	1285
60°	885
65°	698
70°	431
75°	0
80°	0
85°	0



TEST NUMBER: P858322

CATALOG NUMBER: LD4C10W2N2765D010 4LBMLI\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.7	14.3
10°-20°	314.6	31.9
20°-30°	312.8	31.7
30°-40°	170.4	17.3
40°-50°	39.4	4.0
50°-60°	5.6	0.6
60°-70°	2.1	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	768.2	77.9
0°-40°	938.5	95.2
0°-60°	983.5	99.7
0°-90°	986.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	986.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1554	
5°	1522	141
15°	1136	315
25°	686	313
35°	264	170
45°	45	39
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858322

CATALOG NUMBER: LD4C10W2N2765D010 4LBMLI\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1554.4
2.5°	1550.8
5°	1522.1
7.5°	1463.7
10°	1382.6
12.5°	1263.3
15°	1135.7
17.5°	1009.2
20°	885.1
22.5°	783.7
25°	685.9
27.5°	592.9
30°	487.9
32.5°	371.0
35°	263.7
37.5°	177.7
40°	115.7
42.5°	72.7
45°	45.4
47.5°	26.3
50°	13.1
52.5°	7.2
55°	6.0
57.5°	3.6
60°	3.6
62.5°	2.4
65°	2.4
67.5°	1.2
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)