

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859220

Luminaire Tested: **LX4C60D010 EX4C609035 4LBMH**

Issue Date: 2/8/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P859220  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C60D010 EX4C609035 4LBMH  
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBM TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver:


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4863.0 lumens  
Efficiency: N/A  
Efficacy: 67.5 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859220

CATALOG NUMBER: LX4C60D010 EX4C609035 4LBMH

### Luminous Intensity Polar Plot





TEST NUMBER: P859220

CATALOG NUMBER: LX4C60D010 EX4C609035 4LBMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	385084
5°	386555
10°	387731
15°	387743
20°	385612
25°	376582
30°	351980
35°	304797
40°	238107
45°	170840
50°	110987
55°	66420
60°	38871
65°	24971
70°	16595
75°	12531
80°	9339
85°	0



TEST NUMBER: P859220

CATALOG NUMBER: LX4C60D010 EX4C609035 4LBMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	298.5	6.1
10°-20°	860.1	17.7
20°-30°	1269.2	26.1
30°-40°	1252.5	25.8
40°-50°	766.5	15.8
50°-60°	293.8	6.0
60°-70°	91.9	1.9
70°-80°	26.9	0.6
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2427.8	49.9
0°-40°	3680.3	75.7
0°-60°	4740.6	97.5
0°-90°	4863.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4863.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3134	
5°	3134	298
15°	3049	860
25°	2778	1269
35°	2032	1252
45°	983	766
55°	310	294
65°	86	92
75°	26	27
85°	0	4
90°	0	



TEST NUMBER: P859220

CATALOG NUMBER: LX4C60D010 EX4C609035 4LBMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3134.5
2.5°	3141.1
5°	3134.5
7.5°	3127.9
10°	3108.1
12.5°	3081.7
15°	3048.6
17.5°	3009.0
20°	2949.5
22.5°	2883.8
25°	2778.1
27.5°	2646.0
30°	2481.2
32.5°	2276.7
35°	2032.3
37.5°	1761.8
40°	1484.7
42.5°	1227.4
45°	983.3
47.5°	765.3
50°	580.7
52.5°	429.0
55°	310.1
57.5°	217.7
60°	158.2
62.5°	118.9
65°	85.9
67.5°	66.1
70°	46.2
72.5°	33.0
75°	26.4
77.5°	13.2
80°	13.2
82.5°	6.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)