

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859240

Luminaire Tested: **LX4C60D010 EX4C609040 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P859240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C60D010 EX4C609040 4LBMDLI
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5352.1 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859240

CATALOG NUMBER: LX4C60D010 EX4C609040 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P859240

CATALOG NUMBER: LX4C60D010 EX4C609040 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	66	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	63	59	57	55			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	863599
5°	893017
10°	902070
15°	812587
20°	675288
25°	529799
30°	387729
35°	200368
40°	95150
45°	33480
50°	7569
55°	4926
60°	3440
65°	2587
70°	1832
75°	1234
80°	920
85°	0



TEST NUMBER: P859240

CATALOG NUMBER: LX4C60D010 EX4C609040 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	691.6	12.9
10°-20°	1759.8	32.9
20°-30°	1780.7	33.3
30°-40°	907.8	17.0
40°-50°	178.0	3.3
50°-60°	21.5	0.4
60°-70°	9.0	0.2
70°-80°	3.2	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4232.1	79.1
0°-40°	5139.9	96.0
0°-60°	5339.4	99.8
0°-90°	5352.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5352.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7030	
5°	7241	692
15°	6389	1760
25°	3908	1781
35°	1336	908
45°	193	178
55°	23	22
65°	9	9
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P859240

CATALOG NUMBER: LX4C60D010 EX4C609040 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7029.5
2.5°	7094.5
5°	7241.3
7.5°	7325.5
10°	7231.1
12.5°	6913.3
15°	6388.9
17.5°	5770.1
20°	5165.2
22.5°	4538.7
25°	3908.4
27.5°	3280.6
30°	2733.2
32.5°	2059.5
35°	1336.0
37.5°	894.5
40°	593.3
42.5°	372.6
45°	192.7
47.5°	68.9
50°	39.6
52.5°	29.3
55°	23.0
57.5°	17.9
60°	14.0
62.5°	11.5
65°	8.9
67.5°	6.4
70°	5.1
72.5°	3.8
75°	2.6
77.5°	2.6
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)