

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859260

Luminaire Tested: **LX4C60D010 EX4C609050 4LBMDH**

Issue Date: 2/18/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P859260  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/18/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C60D010 EX4C609050 4LBMDH  
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LRMD45 TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4700.0 lumens  
Efficiency: N/A  
Efficacy: 65.3 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859260

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBMDH

### Luminous Intensity Polar Plot





TEST NUMBER: P859260

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBMDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 113 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 104 | 103 | 101 | 101 | 99  | 98  | 97  | 96  | 95  | 93  |    |    |   |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  | 95  | 92  | 90  | 92  | 90  | 88  | 87  |    |    |   |
| 3   | 102 | 96  | 91  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  | 89  | 86  | 83  | 87  | 84  | 82  | 81  |    |    |   |
| 4   | 97  | 90  | 84  | 80  | 95  | 88  | 83  | 79  | 86  | 82  | 78  | 84  | 80  | 77  | 82  | 79  | 77  | 75  |    |    |   |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 77  | 73  | 81  | 76  | 73  | 79  | 75  | 72  | 78  | 74  | 71  | 70  |    |    |   |
| 6   | 88  | 79  | 73  | 68  | 86  | 78  | 72  | 68  | 76  | 71  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 65  |    |    |   |
| 7   | 83  | 74  | 68  | 64  | 82  | 73  | 68  | 64  | 72  | 67  | 63  | 71  | 66  | 63  | 70  | 66  | 63  | 61  |    |    |   |
| 8   | 79  | 70  | 64  | 60  | 78  | 69  | 63  | 60  | 68  | 63  | 59  | 67  | 62  | 59  | 66  | 62  | 59  | 57  |    |    |   |
| 9   | 76  | 66  | 60  | 56  | 74  | 65  | 60  | 56  | 64  | 59  | 56  | 64  | 59  | 56  | 63  | 58  | 55  | 54  |    |    |   |
| 10  | 72  | 62  | 57  | 53  | 71  | 62  | 56  | 53  | 61  | 56  | 53  | 60  | 56  | 52  | 60  | 55  | 52  | 51  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 695609 |
| 5°  | 686229 |
| 10° | 654032 |
| 15° | 605208 |
| 20° | 544811 |
| 25° | 452601 |
| 30° | 329014 |
| 35° | 213266 |
| 40° | 129069 |
| 45° | 66525  |
| 50° | 30121  |
| 55° | 18120  |
| 60° | 12162  |
| 65° | 8721   |
| 70° | 6537   |
| 75° | 4319   |
| 80° | 2759   |
| 85° | 1832   |



TEST NUMBER: P859260

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBMDH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 520.9  | 11.1      |
| 10°-20°   | 1327.8 | 28.3      |
| 20°-30°   | 1501.5 | 31.9      |
| 30°-40°   | 907.4  | 19.3      |
| 40°-50°   | 317.9  | 6.8       |
| 50°-60°   | 81.3   | 1.7       |
| 60°-70°   | 31.2   | 0.7       |
| 70°-80°   | 10.4   | 0.2       |
| 80°-90°   | 1.6    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 3350.2 | 71.3      |
| 0°-40°    | 4257.6 | 90.6      |
| 0°-60°    | 4656.8 | 99.1      |
| 0°-90°    | 4700.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4700.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5662 |      |
| 5°  | 5564 | 521  |
| 15° | 4758 | 1328 |
| 25° | 3339 | 1501 |
| 35° | 1422 | 907  |
| 45° | 383  | 318  |
| 55° | 85   | 81   |
| 65° | 30   | 31   |
| 75° | 9    | 10   |
| 85° | 1    | 2    |
| 90° | 0    |      |



TEST NUMBER: P859260

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBMDH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 5662.1 |
| 2.5°  | 5638.7 |
| 5°    | 5564.5 |
| 7.5°  | 5432.9 |
| 10°   | 5242.8 |
| 12.5° | 5013.6 |
| 15°   | 4758.4 |
| 17.5° | 4478.4 |
| 20°   | 4167.2 |
| 22.5° | 3785.6 |
| 25°   | 3338.9 |
| 27.5° | 2827.2 |
| 30°   | 2319.3 |
| 32.5° | 1833.6 |
| 35°   | 1422.0 |
| 37.5° | 1078.3 |
| 40°   | 804.8  |
| 42.5° | 578.2  |
| 45°   | 382.9  |
| 47.5° | 235.7  |
| 50°   | 157.6  |
| 52.5° | 113.3  |
| 55°   | 84.6   |
| 57.5° | 65.1   |
| 60°   | 49.5   |
| 62.5° | 39.1   |
| 65°   | 30.0   |
| 67.5° | 23.4   |
| 70°   | 18.2   |
| 72.5° | 13.0   |
| 75°   | 9.1    |
| 77.5° | 6.5    |
| 80°   | 3.9    |
| 82.5° | 2.6    |
| 85°   | 1.3    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)