

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858356

Luminaire Tested: **LD4C15W2N2050D010 4LBMH\_2700K**

Issue Date: 11/9/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P858356  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 11/9/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C15W2N2050D010 4LBMH\_2700K  
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, W2N2050 LEDS AND 4LBMH TRIM WITH FINISH  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 975.0 lumens  
Efficiency: N/A  
Efficacy: 50.8 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858356

CATALOG NUMBER: LD4C15W2N2050D010 4LBMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P858356

CATALOG NUMBER: LD4C15W2N2050D010 4LBMH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	118775
5°	117046
10°	112162
15°	105934
20°	98877
25°	89764
30°	74944
35°	54291
40°	33983
45°	19424
50°	10130
55°	5676
60°	3612
65°	2151
70°	1580
75°	712
80°	1061
85°	0



TEST NUMBER: P858356

CATALOG NUMBER: LD4C15W2N2050D010 4LBMH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.0	9.1
10°-20°	233.4	23.9
20°-30°	299.9	30.8
30°-40°	225.7	23.1
40°-50°	90.6	9.3
50°-60°	25.8	2.6
60°-70°	8.2	0.8
70°-80°	2.3	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.3	63.8
0°-40°	847.9	87.0
0°-60°	964.3	98.9
0°-90°	975.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	975.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	967	
5°	949	89
15°	833	233
25°	662	300
35°	362	226
45°	112	91
55°	26	26
65°	7	8
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P858356

CATALOG NUMBER: LD4C15W2N2050D010 4LBMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	966.8
2.5°	960.9
5°	949.1
7.5°	927.0
10°	899.1
12.5°	865.3
15°	832.9
17.5°	796.1
20°	756.3
22.5°	713.7
25°	662.2
27.5°	600.4
30°	528.3
32.5°	447.3
35°	362.0
37.5°	282.5
40°	211.9
42.5°	156.0
45°	111.8
47.5°	76.5
50°	53.0
52.5°	36.8
55°	26.5
57.5°	19.1
60°	14.7
62.5°	10.3
65°	7.4
67.5°	5.9
70°	4.4
72.5°	2.9
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)