

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859276

Luminaire Tested: **LX4C60D010 EX4C609730 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C60D010 EX4C609730 4LBWH
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 97CRI LEDS
AND 4LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5331.0 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859276

CATALOG NUMBER: LX4C60D010 EX4C609730 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P859276

CATALOG NUMBER: LX4C60D010 EX4C609730 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																											
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82																											
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																											
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67																											
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61																											
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55																											
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50																											
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																											
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43																											
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	422137
5°	423749
10°	425044
15°	425060
20°	422728
25°	412829
30°	385856
35°	334132
40°	261024
45°	187275
50°	121652
55°	72824
60°	42630
65°	27355
70°	18211
75°	13765
80°	10259
85°	0



TEST NUMBER: P859276

CATALOG NUMBER: LX4C60D010 EX4C609730 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	327.2	6.1
10°-20°	942.9	17.7
20°-30°	1391.3	26.1
30°-40°	1373.0	25.8
40°-50°	840.2	15.8
50°-60°	322.1	6.0
60°-70°	100.7	1.9
70°-80°	29.5	0.6
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2661.4	49.9
0°-40°	4034.5	75.7
0°-60°	5196.8	97.5
0°-90°	5331.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5331.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3436	
5°	3436	327
15°	3342	943
25°	3046	1391
35°	2228	1373
45°	1078	840
55°	340	322
65°	94	101
75°	29	30
85°	0	4
90°	0	



TEST NUMBER: P859276

CATALOG NUMBER: LX4C60D010 EX4C609730 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3436.1
2.5°	3443.4
5°	3436.1
7.5°	3428.9
10°	3407.2
12.5°	3378.2
15°	3342.0
17.5°	3298.6
20°	3233.4
22.5°	3161.3
25°	3045.5
27.5°	2900.6
30°	2720.0
32.5°	2495.8
35°	2227.9
37.5°	1931.4
40°	1627.6
42.5°	1345.5
45°	1077.9
47.5°	839.0
50°	636.5
52.5°	470.3
55°	340.0
57.5°	238.6
60°	173.5
62.5°	130.3
65°	94.1
67.5°	72.4
70°	50.7
72.5°	36.2
75°	29.0
77.5°	14.5
80°	14.5
82.5°	7.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)