

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859300

Luminaire Tested: **LD4C60D010 EU4609030 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P859300
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C60D010 EU4609030 4LBSH
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7327.5 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 97.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859300

CATALOG NUMBER: LD4C60D010 EU4609030 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P859300

CATALOG NUMBER: LD4C60D010 EU4609030 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	470799
5°	468639
10°	458938
15°	442268
20°	421917
25°	399165
30°	376550
35°	354529
40°	333818
45°	311188
50°	283746
55°	250579
60°	212119
65°	166540
70°	118859
75°	65125
80°	11532
85°	0



TEST NUMBER: P859300

CATALOG NUMBER: LD4C60D010 EU4609030 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	359.0	4.9
10°-20°	975.7	13.3
20°-30°	1354.9	18.5
30°-40°	1478.6	20.2
40°-50°	1379.3	18.8
50°-60°	1046.9	14.3
60°-70°	573.3	7.8
70°-80°	157.8	2.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2689.6	36.7
0°-40°	4168.1	56.9
0°-60°	6594.3	90.0
0°-90°	7327.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7327.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3832	
5°	3800	359
15°	3477	976
25°	2945	1355
35°	2364	1479
45°	1791	1379
55°	1170	1047
65°	573	573
75°	137	158
85°	0	2
90°	0	



TEST NUMBER: P859300

CATALOG NUMBER: LD4C60D010 EU4609030 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3832.2
2.5°	3832.2
5°	3800.1
7.5°	3751.7
10°	3678.9
12.5°	3582.2
15°	3477.3
17.5°	3348.2
20°	3227.2
22.5°	3081.9
25°	2944.7
27.5°	2807.7
30°	2654.4
32.5°	2509.0
35°	2363.9
37.5°	2218.6
40°	2081.5
42.5°	1936.2
45°	1791.1
47.5°	1645.7
50°	1484.6
52.5°	1331.2
55°	1169.9
57.5°	1016.6
60°	863.3
62.5°	710.0
65°	572.9
67.5°	443.7
70°	330.9
72.5°	225.9
75°	137.2
77.5°	64.5
80°	16.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)