

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858371

Luminaire Tested: **LD4C15W2N2050D010 4LBNH\_4000K**

Issue Date: 11/9/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P858371  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 11/9/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C15W2N2050D010 4LBNH\_4000K  
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, W2N2050 LEDS AND 4LBNH TRIM WITH FINISH  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 900.0 lumens  
Efficiency: N/A  
Efficacy: 46.9 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858371

CATALOG NUMBER: LD4C15W2N2050D010 4LBNH\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P858371

CATALOG NUMBER: LD4C15W2N2050D010 4LBNH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	141736
5°	138232
10°	127543
15°	112917
20°	98053
25°	83867
30°	69142
35°	45533
40°	24473
45°	10841
50°	4396
55°	3170
60°	2015
65°	1453
70°	1185
75°	807
80°	1203
85°	0



TEST NUMBER: P858371

CATALOG NUMBER: LD4C15W2N2050D010 4LBNH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.7	11.5
10°-20°	247.4	27.5
20°-30°	283.4	31.5
30°-40°	190.4	21.2
40°-50°	54.4	6.0
50°-60°	13.3	1.5
60°-70°	5.1	0.6
70°-80°	2.0	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	634.6	70.5
0°-40°	825.0	91.7
0°-60°	892.7	99.2
0°-90°	900.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	900.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1154	
5°	1121	104
15°	888	247
25°	619	283
35°	304	190
45°	62	54
55°	15	13
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P858371

CATALOG NUMBER: LD4C15W2N2050D010 4LBNH\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1153.7
2.5°	1145.5
5°	1120.9
7.5°	1076.5
10°	1022.4
12.5°	953.5
15°	887.8
17.5°	818.9
20°	750.0
22.5°	684.3
25°	618.7
27.5°	558.0
30°	487.4
32.5°	393.8
35°	303.6
37.5°	221.5
40°	152.6
42.5°	100.1
45°	62.4
47.5°	37.7
50°	23.0
52.5°	18.0
55°	14.8
57.5°	11.5
60°	8.2
62.5°	6.5
65°	5.0
67.5°	3.3
70°	3.3
72.5°	1.7
75°	1.7
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)