

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859307

Luminaire Tested: **LX4C60D010 EX4C609030 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P859307
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C60D010 EX4C609030 4LBMDLI
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LRMD45 TRIM WITH LI FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6164.7 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 97.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859307

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P859307

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	66	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	63	59	57	55			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	994745
5°	1028610
10°	1039044
15°	935971
20°	777838
25°	610250
30°	446600
35°	230784
40°	109599
45°	38571
50°	8696
55°	5655
60°	3980
65°	2994
70°	2119
75°	1377
80°	1061
85°	0



TEST NUMBER: P859307

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	796.7	12.9
10°-20°	2027.0	32.9
20°-30°	2051.1	33.3
30°-40°	1045.6	17.0
40°-50°	205.0	3.3
50°-60°	24.8	0.4
60°-70°	10.3	0.2
70°-80°	3.7	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4874.7	79.1
0°-40°	5920.3	96.0
0°-60°	6150.1	99.8
0°-90°	6164.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6164.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8097	
5°	8341	797
15°	7359	2027
25°	4502	2051
35°	1539	1046
45°	222	205
55°	26	25
65°	10	10
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P859307

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8097.0
2.5°	8171.9
5°	8340.8
7.5°	8438.0
10°	8329.1
12.5°	7963.2
15°	7359.0
17.5°	6646.2
20°	5949.6
22.5°	5228.0
25°	4501.9
27.5°	3778.7
30°	3148.2
32.5°	2372.2
35°	1538.8
37.5°	1030.3
40°	683.4
42.5°	429.2
45°	222.0
47.5°	79.3
50°	45.5
52.5°	33.8
55°	26.4
57.5°	20.5
60°	16.2
62.5°	13.2
65°	10.3
67.5°	7.3
70°	5.9
72.5°	4.5
75°	2.9
77.5°	2.9
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)