

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858378

Luminaire Tested: **LD4C15W2N2050D010 4LBNLI_5000K**

Issue Date: 11/9/2023

Test Information

Test Method: LM-79-08
Report Number: P858378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15W2N2050D010 4LBNLI_5000K
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2050 LEDS
AND 4LBNLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1101.0 lumens
Efficiency: N/A
Efficacy: 57.3 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 19.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858378

CATALOG NUMBER: LD4C15W2N2050D010 4LBNLI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P858378

CATALOG NUMBER: LD4C15W2N2050D010 4LBNLI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	348081
5°	313240
10°	242836
15°	175760
20°	121704
25°	88720
30°	64461
35°	38139
40°	16037
45°	5004
50°	650
55°	364
60°	418
65°	494
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858378

CATALOG NUMBER: LD4C15W2N2050D010 4LBNLI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.3	20.3
10°-20°	382.3	34.7
20°-30°	303.8	27.6
30°-40°	160.8	14.6
40°-50°	27.7	2.5
50°-60°	2.1	0.2
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	909.4	82.6
0°-40°	1070.2	97.2
0°-60°	1100.0	99.9
0°-90°	1101.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1101.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2833	
5°	2540	223
15°	1382	382
25°	654	304
35°	254	161
45°	29	28
55°	2	2
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858378

CATALOG NUMBER: LD4C15W2N2050D010 4LBNLI_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2833.3
2.5°	2760.4
5°	2540.0
7.5°	2251.8
10°	1946.6
12.5°	1651.5
15°	1381.9
17.5°	1130.9
20°	930.9
22.5°	778.3
25°	654.5
27.5°	554.5
30°	454.4
32.5°	352.7
35°	254.3
37.5°	167.9
40°	100.0
42.5°	57.7
45°	28.8
47.5°	10.2
50°	3.4
52.5°	3.4
55°	1.7
57.5°	1.7
60°	1.7
62.5°	1.7
65°	1.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)