

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858385

Luminaire Tested: **LD4C15W2N2050D010 4LBWH_2000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15W2N2050D010 4LBWH_2000K
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2000K, W2N2050 LEDS AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1042.0 lumens
Efficiency: N/A
Efficacy: 54.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 19.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858385

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_2000K

Luminous Intensity Polar Plot





TEST NUMBER: P858385

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_2000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82508
5°	82824
10°	83083
15°	83079
20°	82626
25°	80695
30°	75412
35°	65315
40°	51015
45°	36607
50°	23776
55°	14244
60°	8329
65°	5349
70°	3556
75°	2706
80°	1981
85°	0



TEST NUMBER: P858385

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_2000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.0	6.1
10°-20°	184.3	17.7
20°-30°	272.0	26.1
30°-40°	268.4	25.8
40°-50°	164.2	15.8
50°-60°	63.0	6.0
60°-70°	19.7	1.9
70°-80°	5.8	0.6
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.2	49.9
0°-40°	788.6	75.7
0°-60°	1015.8	97.5
0°-90°	1042.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1042.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	672	
5°	672	64
15°	653	184
25°	595	272
35°	436	268
45°	211	164
55°	66	63
65°	18	20
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P858385

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_2000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	671.6
2.5°	673.0
5°	671.6
7.5°	670.2
10°	666.0
12.5°	660.3
15°	653.2
17.5°	644.7
20°	632.0
22.5°	617.9
25°	595.3
27.5°	567.0
30°	531.6
32.5°	487.8
35°	435.5
37.5°	377.5
40°	318.1
42.5°	263.0
45°	210.7
47.5°	164.0
50°	124.4
52.5°	91.9
55°	66.5
57.5°	46.6
60°	33.9
62.5°	25.5
65°	18.4
67.5°	14.2
70°	9.9
72.5°	7.1
75°	5.7
77.5°	2.8
80°	2.8
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)