

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859315

Luminaire Tested: **LX4C60D010 EX4C609030 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C60D010 EX4C609030 4LBWH
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBW TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6236.1 lumens
Efficiency: N/A
Efficacy: 64.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 97.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859315

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P859315

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82																			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67																			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61																			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55																			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50																			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43																			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	493810
5°	495696
10°	497211
15°	497226
20°	494503
25°	482910
30°	451367
35°	390868
40°	305336
45°	219070
50°	142312
55°	85183
60°	49854
65°	32006
70°	21301
75°	16091
80°	12027
85°	0



TEST NUMBER: P859315

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	382.8	6.1
10°-20°	1103.0	17.7
20°-30°	1627.6	26.1
30°-40°	1606.2	25.8
40°-50°	982.9	15.8
50°-60°	376.8	6.0
60°-70°	117.8	1.9
70°-80°	34.6	0.6
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3113.3	49.9
0°-40°	4719.4	75.7
0°-60°	6079.1	97.5
0°-90°	6236.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6236.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4020	
5°	4020	383
15°	3909	1103
25°	3562	1628
35°	2606	1606
45°	1261	983
55°	398	377
65°	110	118
75°	34	35
85°	0	5
90°	0	



TEST NUMBER: P859315

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4019.5
2.5°	4028.0
5°	4019.5
7.5°	4011.0
10°	3985.7
12.5°	3951.7
15°	3909.4
17.5°	3858.6
20°	3782.4
22.5°	3698.0
25°	3562.5
27.5°	3393.1
30°	3181.8
32.5°	2919.6
35°	2606.2
37.5°	2259.3
40°	1903.9
42.5°	1573.9
45°	1260.9
47.5°	981.4
50°	744.6
52.5°	550.1
55°	397.7
57.5°	279.1
60°	202.9
62.5°	152.4
65°	110.1
67.5°	84.7
70°	59.3
72.5°	42.3
75°	33.9
77.5°	17.0
80°	17.0
82.5°	8.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)