

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858388

Luminaire Tested: **LD4C15W2N2050D010 4LBWH_3500K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858388
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15W2N2050D010 4LBWH_3500K
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, W2N2050 LEDS AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1241.0 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 19.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858388

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P858388

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98270
5°	98646
10°	98951
15°	98952
20°	98406
25°	96108
30°	89825
35°	77778
40°	60766
45°	43592
50°	28325
55°	16942
60°	9927
65°	6366
70°	4239
75°	3180
80°	2405
85°	0



TEST NUMBER: P858388

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.2	6.1
10°-20°	219.5	17.7
20°-30°	323.9	26.1
30°-40°	319.6	25.8
40°-50°	195.6	15.8
50°-60°	75.0	6.0
60°-70°	23.4	1.9
70°-80°	6.9	0.6
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.6	49.9
0°-40°	939.2	75.7
0°-60°	1209.7	97.5
0°-90°	1241.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1241.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	800	
5°	800	76
15°	778	219
25°	709	324
35°	519	320
45°	251	196
55°	79	75
65°	22	23
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P858388

CATALOG NUMBER: LD4C15W2N2050D010 4LBWH_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	799.9
2.5°	801.6
5°	799.9
7.5°	798.2
10°	793.2
12.5°	786.4
15°	778.0
17.5°	767.9
20°	752.7
22.5°	735.9
25°	709.0
27.5°	675.2
30°	633.2
32.5°	581.0
35°	518.6
37.5°	449.6
40°	378.9
42.5°	313.2
45°	250.9
47.5°	195.3
50°	148.2
52.5°	109.5
55°	79.1
57.5°	55.5
60°	40.4
62.5°	30.3
65°	21.9
67.5°	16.9
70°	11.8
72.5°	8.4
75°	6.7
77.5°	3.4
80°	3.4
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)