

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858392

Luminaire Tested: **LD4C15W2N2050D010 4LBWLI_2700K**

Issue Date: 11/9/2023

Test Information

Test Method: LM-79-08
Report Number: P858392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15W2N2050D010 4LBWLI_2700K
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, W2N2050 LEDS AND 4LBWLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1283.0 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 19.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858392

CATALOG NUMBER: LD4C15W2N2050D010 4LBWLI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P858392

CATALOG NUMBER: LD4C15W2N2050D010 4LBWLI_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96575
5°	98214
10°	102656
15°	108949
20°	113729
25°	112740
30°	104848
35°	89686
40°	68335
45°	40082
50°	17125
55°	5033
60°	1450
65°	843
70°	539
75°	712
80°	0
85°	0



TEST NUMBER: P858392

CATALOG NUMBER: LD4C15W2N2050D010 4LBWLI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.9	6.0
10°-20°	242.6	18.9
20°-30°	378.5	29.5
30°-40°	368.2	28.7
40°-50°	183.9	14.3
50°-60°	28.5	2.2
60°-70°	3.4	0.3
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	697.9	54.4
0°-40°	1066.2	83.1
0°-60°	1278.6	99.7
0°-90°	1283.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1283.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	786	
5°	796	77
15°	857	243
25°	832	378
35°	598	368
45°	231	184
55°	24	28
65°	3	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P858392

CATALOG NUMBER: LD4C15W2N2050D010 4LBWLI_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	786.1
2.5°	789.0
5°	796.4
7.5°	808.2
10°	822.9
12.5°	841.9
15°	856.6
17.5°	868.4
20°	869.9
22.5°	859.6
25°	831.7
27.5°	790.5
30°	739.1
32.5°	674.5
35°	598.0
37.5°	514.3
40°	426.1
42.5°	332.1
45°	230.7
47.5°	148.4
50°	89.6
52.5°	48.5
55°	23.5
57.5°	10.3
60°	5.9
62.5°	4.4
65°	2.9
67.5°	2.9
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)